

ZCEF2

Limit switch head, Limit switches XC Standard, ZCE, M12 steel roller plunger



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	M12 plunger head
Product Compatibility	XCKT XCKP XCKD XCMD
Associated body	ZCMD81L2 ZCMD41L2 ZCMD25L1 ZCMD21M12 ZCMD39L1 ZCMD29L2 ZCMD37L5 ZCMD21L2 ZCMD41L5 ZCMD61M12 ZCMD29C12 ZCMD25L2 ZCMD21C12 ZCMD21L1 ZCMD21L08U78 ZCMD21L08R12 ZCMD29L5 ZCMD81L1 ZCMD37L2 ZCMD21L5 ZCMD29L1 ZCMD39L2 ZCMD61C12 ZCMD81L5 ZCMD25L5 ZCMD37L1 ZCMD69C12 ZCMD39L5 ZCMD41L1
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191028
Nbr. of units in pkg.	1
Package weight(Lbs)	1.34 oz (38.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	0.59 in (1.5 cm)
Package 1 Length	1.97 in (5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------