



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	M16 plunger head
Product Compatibility	XCKP XCKD XCKT XCMD
Associated body	ZCMD21L08U78 ZCMD41L1 ZCMD81L5 ZCMD61M12 ZCMD21M12 ZCMD37L1 ZCMD81L1 ZCMD29C12 ZCMD21L5 ZCMD39L1 ZCMD21L2 ZCMD41L2 ZCMD21C12 ZCMD21L1 ZCMD37L2 ZCMD39L5 ZCMD29L5 ZCMD29L1 ZCMD29L2 ZCMD61C12 ZCMD25L1 ZCMD39L2 ZCMD81L2 ZCMD41L5 ZCMD25L5 ZCMD69C12 ZCMD21L08R12 ZCMD25L2 ZCMD37L5
Movement of operating head	Linear
Type of operator	End plunger spring return metal with nitrile boot)
Type of approach	Vertical approach, 1 direction

Complementary

Positive opening	With
------------------	------

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110190939
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	2.17 in (5.5 cm)
Package 1 Length	1.18 in (3.0 cm)
Package 1 Weight	1.83 oz (52.0 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	5.51 in (14.0 cm)
Package 2 Width	1.57 in (4.0 cm)
Package 2 Length	3.54 in (9.0 cm)
Package 2 Weight	18.38 oz (521.0 g)
Unit Type of Package 3	S01
Number of Units in Package 3	50
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	6.32 lb(US) (2.868 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------