



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	M18 plunger head
Product Compatibility	XCMD XCKD XCKT XCKP
Associated body	ZCP31 ZCT25P16 ZCT28P16 ZCD35 ZCP21 ZCT27N12 ZCD26 ZCP28 ZCT26P16 ZCP27 ZCP37 ZCT27G11 ZCD31 ZCT28G11 ZCP25 ZCT21N12 ZCD21 ZCT21G11 ZCD29M12 ZCT26G11 ZCP21M12 ZCD25 ZCD37 ZCD29 ZCT25G11 ZCD28 ZCT28N12 ZCT26N12 ZCP29 ZCD21M12 ZCT21P16 ZCP35 ZCT27P16 ZCP29M12 ZCT25N12 ZCP39 ZCD27 ZCD39 ZCP26
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191042
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	2.76 in (7.0 cm)
Package 1 Weight	2.36 oz (67.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------