

ZCKY14

Limit switch lever, Limit switches XC Standard, ZCKY, steel roller ball bearing mounted, -40...120 °C



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch lever
Device short name	ZCKY
Product Compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal ball bearing mounted)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Environmental characteristic	Standard environment High temperature Low temperature

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646313
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2 cm)
Package 1 Width	0.91 in (2.3 cm)
Package 1 Length	2.05 in (5.2 cm)
Package 1 Weight	0.99 oz (28 g)
Unit Type of Package 2	S01
Number of Units in Package 2	100
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)

Package 2 Length	15.75 in (40 cm)
Package 2 Weight	6.84 lb(US) (3.102 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------