

# ZCKY49

Limit switch lever, Limit switches XC Standard, ZCKY, elastomer roller Ø 50 mm variable length



## Main

|                            |                                                                              |
|----------------------------|------------------------------------------------------------------------------|
| Range of Product           | Telemecanique Limit switches XC Standard                                     |
| Series name                | Standard format                                                              |
| Product or Component Type  | Limit switch lever                                                           |
| Device short name          | ZCKY                                                                         |
| Product Compatibility      | XCKL<br>XCKM<br>XCKS                                                         |
| Associated head            | ZCKD05                                                                       |
| Movement of operating head | Rotary                                                                       |
| Type of operator           | Roller lever spring return elastomer variable length, roller diameter 50 mm) |
| Type of approach           | Lateral approach                                                             |

## Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without    |

## Environment

|                                       |                                                 |
|---------------------------------------|-------------------------------------------------|
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) standard environment |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C) standard environment |
| Environmental characteristic          | Standard environment                            |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 22411-LIMIT SWITCHES,IEC,XCKJ |
| Discount Schedule     | T                             |
| GTIN                  | 3389110735857                 |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 1.45 oz (41.0 g)              |
| Returnability         | Yes                           |
| Country of origin     | FR                            |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Package 1 Height             | 0.98 in (2.5 cm)       |
| Package 1 width              | 3.94 in (10 cm)        |
| Package 1 Length             | 3.94 in (10 cm)        |
| Unit Type of Package 2       | S01                    |
| Number of Units in Package 2 | 70                     |
| Package 2 Weight             | 6.71 lb(US) (3.042 kg) |
| Package 2 Height             | 5.91 in (15 cm)        |
| Package 2 width              | 5.91 in (15 cm)        |
| Package 2 Length             | 15.75 in (40 cm)       |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                 |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                               |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                               |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                     |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|