

**MODEL:** CEP-2224 | **DESCRIPTION:** PIEZO BUZZER INDICATOR**FEATURES**

- through-hole pins
- 12 Vdc rating
- 3.4 kHz rated frequency
- low profile

**SPECIFICATIONS**

| parameter             | conditions/description  | min   | typ   | max   | units |
|-----------------------|-------------------------|-------|-------|-------|-------|
| rated voltage         |                         |       | 12    |       | Vdc   |
| operating voltage     |                         | 3     |       | 20    | Vdc   |
| current consumption   | at rated voltage        |       |       | 15    | mA    |
| rated frequency       |                         | 2,900 | 3,400 | 3,900 | Hz    |
| sound pressure level  | at 30 cm, rated voltage | 78    |       |       | dB    |
| dimensions            | Ø24.0 x 9.0             |       |       |       | mm    |
| weight                |                         |       |       | 1.2   | g     |
| material              | ABS PA-777D (black)     |       |       |       |       |
| terminal              | pin type (Sn plating)   |       |       |       |       |
| operating temperature |                         | -30   |       | 85    | °C    |
| storage temperature   |                         | -40   |       | 95    | °C    |
| RoHS                  | yes                     |       |       |       |       |

Notes: 1. All specifications measured at 5-35°C, humidity at 45-85%, under 86-106kPa pressure, unless otherwise noted.


**SOLDERABILITY**

| parameter                   | conditions/description | min | typ | max | units |
|-----------------------------|------------------------|-----|-----|-----|-------|
| hand soldering <sup>2</sup> | for maximum 2 seconds  | 330 |     | 380 | °C    |

Notes: 2. Not recommended for wave soldering


MECHANICAL DRAWING

units: mm  
tolerance: ±0.5 mm



PERFORMANCE CURVES

P: Voltage vs. Sound Pressure Level  
I: Voltage vs. Current Consumption



## PACKAGING


Inner Unit Size: 305 x 245 x 49 mm

Carton Size: 530 x 330 x 280 mm

Tray QTY: 125 pcs per tray

Inner Unit QTY: 250 pcs per unit

Carton QTY: 2,500 pcs per carton



REVISION HISTORY

| rev. | description                       | date       |
|------|-----------------------------------|------------|
| 1.0  | initial release                   | 09/19/2006 |
| 1.01 | applied new spec template         | 03/19/2019 |
| 1.02 | brand update                      | 10/11/2019 |
| 1.02 | logo, datasheet style update      | 08/05/2022 |
| 1.03 | CUI Devices rebranded to Same Sky | 09/11/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**