

MODEL: CPT-5828-108L170

| DESCRIPTION: PIEZO BUZZER TRANSDUCER

FEATURES

- high SPL
- operating voltage 3-85 V
- screw holes



SPECIFICATIONS

| parameter                 | conditions/description                                | min    | typ    | max    | units |
|---------------------------|-------------------------------------------------------|--------|--------|--------|-------|
| rated voltage             | <div> <div>vp-p</div> <div>0V</div> </div>            |        | 85     |        | Vp-p  |
| operating voltage         |                                                       | 3      |        | 85     | Vp-p  |
| current consumption       | at rated voltage, 2,700 Hz, ½ duty square wave        |        |        | 90     | mA    |
| rated frequency           |                                                       |        | 2,700  |        | Hz    |
| sound pressure level      | at 30 cm, rated voltage, 2,700 Hz, ½ duty square wave | 103    | 108    |        | dB    |
| electrostatic capacitance | at 120 Hz/1 V                                         | 24,500 | 35,000 | 45,500 | pF    |
| dimensions                | 58.5 x 52.8 x 28.3                                    |        |        |        | mm    |
| weight                    |                                                       |        |        | 26     | g     |
| material                  | ABS                                                   |        |        |        |       |
| terminal                  | wire leads                                            |        |        |        |       |
| operating temperature     |                                                       | -20    |        | 70     | °C    |
| storage temperature       |                                                       | -30    |        | 85     | °C    |
| washable                  | no                                                    |        |        |        |       |
| RoHS                      | yes                                                   |        |        |        |       |

Notes:

1. All specifications measured at 5-35°C, humidity at 45-85%, under 86-106 kPa pressure, unless otherwise noted.


SOLDERABILITY

| parameter      | conditions/description | min | typ | max | units |
|----------------|------------------------|-----|-----|-----|-------|
| hand soldering | for maximum 3 seconds  |     |     | 380 | °C    |


## MECHANICAL DRAWING

units: mm  
tolerance:  $\pm 0.5$  mm


wire: UL1007 24AWG



## FREQUENCY RESPONSE CURVE



## APPLICATION CIRCUIT




## PACKAGING

units: mm

Carton Size: 360 x 270 x 280 mm

Carton QTY: 200 pcs per carton



## REVISION HISTORY

| rev. | description                       | date       |
|------|-----------------------------------|------------|
| 1.0  | initial release                   | 12/11/2019 |
| 1.01 | logo, datasheet style update      | 08/05/2022 |
| 1.02 | CUI Devices rebranded to Same Sky | 09/11/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**