


**SERIES:** TS36 | **DESCRIPTION:** TACTILE SWITCH**FEATURES**

- surface mount
- IP67
- halogen & halogen free

**SPECIFICATIONS**





parameter	conditions/description	min	typ	max	units
rated voltage		1		12	Vdc
rated current		0.01		50	mA
withstanding voltage	for 1 minute		250		Vac
contact resistance				100	mΩ
insulation resistance	at 250 Vdc	100			MΩ
operating force	160 gf models 260 gf models	110 190	160 260	210 330	gf gf
return force		50			gf
actuator travel		0.15	0.25	0.45	mm
operating temperature		-40		90	°C
storage temperature		-40		90	°C
life	at 5 Vdc, 5 mA, 2 cycles/second, 1.5 times operating force		100,000		cycles
vibration	10~55~10 Hz, 1.5 mm amplitude, 2 hours on each XYZ				
flammability rating	see material table				
RoHS	yes				
IP level	IP67				

PART NUMBER KEY

MECHANICAL DRAWING (WITHOUT GROUND)

units: mm
tolerance:
L≤10: ±0.3
10<L≤100: ±0.5
100<L: ±0.6
unless otherwise specified

DESCRIPTION	MATERIAL	PLATING/COLOR
terminal	brass	silver
housing	PA6T (halogen models) PPA (halogen free models)	black
dome	stainless steel	silver
stem	FR52 (halogen models) PPA (halogen free models)	black
waterproof mat	rubber	
cover	stainless steel	







Recommended PCB Layout
Top View

Model	Actuator Height, H (mm)
31	3.1 mm
35	3.5 mm

MECHANICAL DRAWING (WITH GROUND)

units: mm
tolerance:
L≤10: ±0.3
10<L≤100: ±0.5
100<L: ±0.6
unless otherwise specified

DESCRIPTION	MATERIAL	PLATING/COLOR
terminal	brass	silver
housing	PA6T (halogen models) PPA (halogen free models)	black black
dome	stainless steel	silver
stem	FR52 (halogen models) PPA (halogen free models)	black black
waterproof mat	rubber	
cover	stainless steel	




Recommended PCB Layout
Top View

Model	Actuator Height, H (mm)
31	3.1 mm
35	3.5 mm

SOLDERABILITY


parameter	conditions/description	min	typ	max	units
reflow soldering			260		°C



PACKAGING

units: mm

Reel QTY: 1,500 pcs



Puling-out direction the tape

REVISION HISTORY

rev.	description	date
1.0	initial release	12/09/2024

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com