


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

REVISI			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/25/2022	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-M3LC-STS-02	2.0 [6.56]
FCA-M3LC-STS-05	5.0 [16.40]
FCA-M3LC-STS-10	10.0 [32.81]
FCA-M3LC-STS-15	15.0 [49.21]

NOTES:

1. LC CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
2. ST CONNECTOR 1 ASSEMBLY POLISH TYPE: UPC.
3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com TM an INFINIT [®] brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY KGLEBOVA	04/18/22	CATEGORY FIBER OPTICS	PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD MM OM3 SIMPLEX 3.0mm LC/UPC-ST/UPC ARMORED LSZH BLACK
	CHECKED BY PHOSPODAR	04/25/22		
	APPROVED BY PHOSPODAR	04/25/22		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	CAGE CODE 43321	ITEM NO. FCA-M3LC-STS
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	REV. A	SCALE: NONE	CAD FILE: FCA-M3LC-STS.SLDDRW
				SHEET 1 OF 1