


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION | | | | | |
|----------|-----|-------------|------------|------------|-----------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | B | ECO-12395 | 08/25/2023 | DMAY | PHOSPODAR |



| PART NUMBER | LENGTH METERS [FEET] |
|---------------|----------------------|
| FOA2ODD8-001M | 1.0 [3.28] |
| FOA2ODD8-002M | 2.0 [6.56] |
| FOA2ODD8-005M | 5.0 [16.40] |
| FOA2ODD8-010M | 10.0 [32.80] |
| FOA2ODD8-012M | 12.0 [39.37] |

| | | | | |
|---|--|-------------------------------|---|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] | APPROVALS | DATE | L-com TM an INFINIT [®] brand | 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY MVEERAPPAN | 2/6/2021 | | |
| OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 | CHECKED BY DFRISIELLO | 08/02/2021 | CATEGORY | FIBER OPTIC |
| | APPROVED BY PHOSPODAR | 08/02/2021 | | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1° | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION | SIZE A CAGE CODE 43321 ITEM NO. FOA2ODD8 | REV. B |
| | THIRD-ANGLE PROJECTION | COLOR VARIATIONS MAY OCCUR | | |
| | | SCALE: NONE | CAD FILE: FOA2ODD8.SLDDRW | SHEET 1 OF 1 |