

Fiber Enclosure Wall Mount with 24 LC/APC Duplex Adapters & 48 LC/APC Pigtailed



LCWB-24LCAP

Features

- Low profile fiber optic wall mount enclosure
- SPCC Steel
- Includes 24 LC/APC duplex adapters and 48 LC/APC 2.0mm pigtailed
- Fiber management rings ensure bend radius larger than 40mm
- Secure lid latch, set of 2 keys
- Operational temp -40°C to 60°C

Applications

- FTTH Access Networks
- Telecommunication Networks
- CATV Networks
- Data Communications Networks
- LAN (Local Area Network) deployments
- Data Centers

Description

Introducing the LCWB-24LCAP, a versatile indoor fiber optic distribution management enclosure designed to streamline connectivity in various networking environments. Crafted from sturdy SPCC Steel, this enclosure ensures long-lasting performance and protection for your fiber optic connections. The L-com LCWB-24LCAP comes equipped with 24 LC/APC duplex adapters installed and 48 LC/APC single mode 2.0mm pigtailed, ready for splicing, providing ample capacity to accommodate your networking needs.

L-com's LCWB-24LCAP cable management is facilitated by fiber management rings that maintain a bend radius larger than 40mm, minimizing signal loss and optimizing performance. The secure lid latch, accompanied by a set of 2 keys, offers added security for your network infrastructure, ensuring peace of mind in high-traffic environments. All the cross-connectivity functions of splicing, termination, and fiber optic distribution for your plant, backbone and in-building fiber cabling can be included in the termination enclosures to protect and ease the organization of your installations.

Operational across temperatures ranging from -40°C to 60°C, the L-com LCWB-24LCAP excels in a variety of indoor networking applications, including FTTH access networks, telecommunication networks, CATV networks, data communications networks, LAN deployments, and data centers. Whether in small-scale setups or large-scale deployments, this low-profile indoor fiber optic wall mount enclosure delivers reliability, security, and performance to meet your networking requirements.

Mechanical Specifications

Size

Outer Height	3.15 in	[80.01 mm]
Outer Width	15.95 in	[405.13 mm]
Outer Depth	17.91 in	[454.91 mm]
Weight	16.5 lbs	[7.48 kg]
Enclosure Material	SPCC Steel	

Environmental Specifications

Temperature Continuous

-40 to 60°C

Fiber Enclosure Wall Mount with 24 LC/APC Duplex Adapters & 48 LC/APC Pigtailed

LCWB-24LCAP



Fiber Enclosure Wall Mount with 24 LC/APC Duplex Adapters & 48 LC/APC Pigtailed from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/fiber-enclosure-wall-mount-24-lc-apc-duplex-adapters-48-lc-apc-pigtails-lcwb-24lcap-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCWB-24LCAP CAD Drawing

Fiber Enclosure Wall Mount with 24 LC/APC Duplex Adapters & 48 LC/APC Pigtailed

