

6

5

4

3

2

1

F

E

D

C

B

A

F

E


D

C

B

A

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	C	ECO-15414	01/16/2026	DMAY	DGUST



NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec
CONDUCTOR RESISTANCE $\leq 22.4\Omega/1000M$
VOLTAGE RATING AC 300V
- CABLE MARKING :
(UL) E135710-F5 SJT 3X18AWG 105°C 300V VW-1
c(UL) SJT 3X0.824mm²(18AWG) 105°C 300V FT2
- OPTIONAL LABELS:
OPTIONAL LABEL(S) MAY INCLUDE
UL, CURRENT AND/OR WARNING
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

LC LG Rev-D4 Asize

6

5

4

3

2

1

ITEM NUMBER	LENGTH (L1) INCHES [MM]	LENGTH (L2) INCHES [MM]
C14-C132-10-2F	24.0 $\pm$ 0.4 [610 $\pm$ 10.0]	9.0 $\pm$ 0.4 [228 $\pm$ 10.0]
C14-C132-10-3F	36.0 $\pm$ 0.4 [915 $\pm$ 10.0]	9.0 $\pm$ 0.4 [228 $\pm$ 10.0]
C14-C132-10-4F	48.0 $\pm$ 0.8 [1220 $\pm$ 20.0]	9.0 $\pm$ 0.4 [228 $\pm$ 10.0]
C14-C132-10-6F	72.0 $\pm$ 0.8 [1830 $\pm$ 20.0]	24.0 $\pm$ 0.4 [609 $\pm$ 10.0]

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = ± 2 [5]	FRACTIONS $\pm 1/32$
.XX = ± 0.02 [0.5]	ANGLES $\pm 1^\circ$
.XXX = ± 0.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤ 12 [305] = ± 1 [25] / -0	
>12 [305] ≤ 60 [1524] = ± 2 [51] / -0	
>60 [1524] ≤ 120 [3048] = ± 4 [102] / -0	
>120 [3048] ≤ 300 [7620] = ± 6 [152] / -0	
>300 [7620] = $\pm 5\%$ / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	

L-com
an INFINIT® brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

SHEET
1 OF 1

DESCRIPTION				
C14 - 2C13 SPLIT POWER CORD, 10A, 250V				
SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	MVEERAPPAN	C14-C132-10	C