



ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-15414	1/16/2026	DMAY	DGUST



## NOTES:

1. VOLTAGE RATING:  
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 SEC  
CONDUCTOR RESISTANCE  $\leq 8.88\Omega/1000m$   
VOLTAGE RATING AC 300V
2. CABLE MARKING:  
(UL) E135710-F5 SJT 3x14AWG 105°C 300V VW-1  
c(UL)SJT 3x2.08mm<sup>2</sup> (14AWG) 105°C 300V FT2
3. OPTIONAL LABELS:  
OPTIONAL LABEL(S) MAY INCLUDE  
UL, CURRENT AND/OR WARNING
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.



ITEM NUMBER	LENGTH (L1) INCHES [mm]	LENGTH (L2) INCHES [mm]
C20-C132-15-2F	$24.0 \pm 0.4$ [610 ± 10]	$9.0 \pm 0.4$ [228 ± 10]
C20-C132-15-3F	$36.0 \pm 0.4$ [915 ± 10]	$12.0 \pm 0.4$ [304 ± 10]
C20-C132-15-4F	$48.0 \pm 0.8$ [1220 ± 20]	$12.0 \pm 0.4$ [304 ± 10]
C20-C132-15-6F	$72.0 \pm 0.8$ [1830 ± 20]	$24.0 \pm 0.4$ [609 ± 10]

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 $X = \pm 0.2$  [5]  
 $XX = \pm 0.02$  [0.5]  
 $XXX = \pm .005$  [0.13]

FRACTIONS  
 $\pm 1/32$   
ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\leq 12$  [305] =  $\pm 1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $\pm 2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $\pm 4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $\pm 6$  [152] / -0  
 $> 300$  [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE<sup>®</sup> brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE  
NONE

1 OF 1

DESCRIPTION  
C20 - 2C13 SPLIT POWER CORD, 15A, 250V

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	MVEERAPPAN	C20-C132-15	B