

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/18/2025	HBAKKE	KHIETPAS

F

F

E

E

D

D

C


C

B

B

A

A



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

$X = \pm .2$ [5]	FRACTIONS $\pm 1/32$
$XX = \pm .02$ [0.5]	
$XXX = \pm .005$ [0.13]	ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:

≤ 12 [305] = $+1$ [25] / -0
> 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
> 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
> 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
> 300 [7620] = $+5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND COLOR
COLORS MAY VARY

L-com
an INFINITE brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

SHEET
1 OF 1

DESCRIPTION
144 / 430MHz, 2.15 / 2.5 dBi, ANTENNA, UHF MALE

SIZE A	CAGE CODE 43321	DRAWN BY HBAKKE	ITEM NO. LCANRBD1078	REV A
-----------	--------------------	--------------------	-------------------------	----------

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.