

6

5

4

3

2

1

F

E

D

C

B

A

F

E




D

C

B

A

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	1	INITIAL RELEASE	10/16/2024	HBAKKE	THOUGHTON



NOTES:

1. MATERIAL: PVC, UL94V-0 COMPLIANT
2. COLOR: BLACK
3. COMPONENT SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

LC LG Rev-D5 Asize

6

5

4

3

2

1

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		L-com® an INFINIT@ brand Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5		
TOLERANCES:				SCALE	SHEET	
.X = ±.2 [5]		FRACTIONS		NONE	1 OF 1	
.XX = ±.02 [0.5]		± 1/32				
.XXX = ±.005 [0.13]		ANGLES ± 1°				
CABLE LENGTH TOLERANCES:		DESCRIPTION				
≤12 [305] = +1 [25] / -0						
>12 [305] ≤ 60 [1524] = +2 [51] / -0						
>60 [1524] ≤ 120 [3048] = +4 [102] / -0						
>120 [3048] ≤ 300 [7620] = +6 [152] / -0						
>300 [7620] = +5% / -0		RACEWAY SPLICE FITTING, 20X35mm BLACK				
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY		SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
		A	43321	HBAKKE	LCSR20x35-SC-B	1