


## REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	02/03/2025	DMAY	DGUTTADAURO

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
 $X = \pm .2$  [5]      FRACTIONS  
 $XX = \pm .02$  [0.5]       $\pm 1/32$   
 $XXX = \pm .005$  [0.13]      ANGLES  $\pm 1^\circ$

CABLE LENGTH TOLERANCES:  
 $\le 12$  [305] =  $\pm 1$  [25] / -0  
 $> 12$  [305]  $\le 60$  [1524] =  $\pm 2$  [51] / -0  
 $> 60$  [1524]  $\le 120$  [3048] =  $\pm 4$  [102] / -0  
 $> 120$  [3048]  $\le 300$  [7620] =  $\pm 6$  [152] / -0  
 $> 300$  [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY

**L-com**  
an INFINITE brand

Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE      SHEET  
NONE      1 OF 1

DESCRIPTION  
CATEGORY 6A ULTRA SHORT-BODY TOOLLESS KEYSTONE  
JACK, UNSHIELDED, RED

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	DMAY	RJSBTLC6A-RED	A