



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/16/2022	GUTTADAURO




"J1"
USB 3.0 TYPE "B"
FEMALE CONNECTOR
30u" GOLD PLATED CONTACTS
NICKEL PLATED SHELL




RECOMMENDED
PANEL CUTOUT



"J2"
USB 3.0 TYPE "A"
FEMALE CONNECTOR
30u" GOLD PLATED CONTACTS
NICKEL PLATED SHELL



"J1" WIRING MAP "J2"



NOTES:

1. ADAPTER HOUSING: ABS, UL94V-0 RATED, BLACK
ADAPTER SHIELDING: STAINLESS STEEL
ADAPTER PCB: GLASS FIBER EPOXY; FR-4,UL94 V-0
2. RATING:
CURRENT: 1.8A (P1 and P4 CONTACT); 0.25A(OTHER CONTACT)
OPERATING TEMPERATURE: -10°C TO +70°C.
3. ADAPTER SHALL BE TESTED FOR CONTINUITY.
4. ADAPTER SHALL BE INDIVIDUALLY PACKAGED
IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
<12 [305] = +1 [25] / -0
>12 [305] ≤60 [1524] = +2 [51] / -0
>60 [1524] ≤120 [3048] = +4 [102] / -0
>120 [3048] ≤300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL OTHER DIMENSIONAL TOLERANCES:
.X = ± .2 [5] FRACTIONS
.XX = ± .02 [5] ± 1/32
.XXX = ± .005 [1.3] ANGLES ± 1°



APPROVALS	DATE
DRAWN BY B.ZHANG	01/18/2022
CHECKED BY GUTTADAURO	01/18/2022
APPROVED BY GUTTADAURO	01/18/2022

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

COLOR VARIATIONS
MAY OCCUR



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

USB

PRODUCT DESCRIPTION

KEYSTONE USB3.0 ADPT, BF-AF, SHLD

SIZE	CAGE CODE	DWG. NO.	REV.
A	43321	U3KEY-BA-S	A
SCALE: NONE	CAD FILE: U3KEY-BA-S.SLDDRW		SHEET 1 OF 1