



Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut for 78 Ohm M17/176-00002, 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3MSA00442-24

Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3MSA00442-24 78 ohm TRB plug to Blunt cut genderless 24 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3MSA00442-24 TRB plug to Blunt cut genderless cable assembly operates to 10 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|------------------------|---------|------------|---------|--------------|
| Frequency Range | DC | | 10 | MHz |
| Capacitance | | 24 [78.74] | | pF/ft [pF/m] |
| Operating Voltage (AC) | | | 750,000 | Vrms |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-------------|----|----|----|----|----|-------|
| Frequency | 1 | 3 | 5 | 7 | 10 | MHz |

Insertion Loss (Typ.)

Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut for 78 Ohm M17/176-00002, 24" Cable PE3MSA00442-24](#)



Lead Free Bend Relief 3-Slot TRB Plug with Blunt
Cut for 78 Ohm M17/176-00002, 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3MSA00442-24

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length* 24 in [609.6 mm]
Weight 0.086 lbs [39.01 g]

Cable

Cable Type M17/176-00002
Impedance 78 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PTFE
Shield Layer 1 Silver Plated Copper
Jacket Material PFA, Blue

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------------|------------------------------|----------------------|
| Type | TRB Plug | Blunt Cut Genderless |
| Impedance | 78 Ohms | |
| Contact Material and Plating | Bronze, Gold 30 micro inches | |
| Contact Plating Specification | ASTM-B-488 | |
| Dielectric Type | Teflon | |
| Outer Conductor Material and Plating | Phosphor Bronze, Gold | |
| Outer Conductor Plating Specification | 30 micro inches | |
| Body Material and Plating | Brass, Nickel | |
| Body Plating Specification | ASTM-B-733 | |

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut for 78 Ohm M17/176-00002, 24" Cable PE3MSA00442-24](#)



Lead Free Bend Relief 3-Slot TRB Plug with Blunt
Cut for 78 Ohm M17/176-00002, 24" Cable

RF Cable Assemblies Technical Data Sheet

PE3MSA00442-24

How to Order

Part Number Configuration:

PE3MSA00442

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MSA00442-12 = 12 inches long cable
PE3MSA00442-100cm = 100 cm long cable

Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut for 78 Ohm M17/176-00002, 24" Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut for 78 Ohm M17/176-00002, 24" Cable PE3MSA00442-24](https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-24-inch-length-using-m17-176-00002-pe3msa00442-24)



URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-24-inch-length-using-m17-176-00002-pe3msa00442-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3MSA00442-24 CAD Drawing

Lead Free Bend Relief 3-Slot TRB Plug with Blunt Cut
for 78 Ohm M17/176-00002, 24" Cable

LEAD FREE SOLDER



| ITEM NUMBER | LENGTH | |
|----------------|--------|--------|
| | FEET | METERS |
| PE3MSA00442-12 | 1.0 | .31 |
| PE3MSA00442-24 | 2.0 | .61 |
| PE3MSA00442-36 | 3.0 | .92 |
| PE3MSA00442-48 | 4.0 | 1.22 |
| PE3MSA00442-60 | 5.0 | 1.52 |

NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| | | | |
|---|------|---|-------------|
| <p>PE3 PASTERNAK® an INFINIT® brand</p> | | <p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> | |
| Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920 | | SCALE | NONE |
| DESCRIPTION | | SHEET | 1 OF 1 |
| LEAD FREE HT 1553 TWINX PLUG BR-BLUNT | | | |
| SIZE | A | CAGE CODE | 53919 |
| DRAWN BY | DMAY | ITEM NO. | PE3MSA00442 |
| REV | A | | |

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ±.2 [.5] FRACTIONS ±.102 [.25] ANGLES ± 1°

.XX = ±.02 [.5] ±.102 [.25] ANGLES ± 1°

.XXX = ±.005 [.13] ±.102 [.25] ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤12 [305] = +.1 [25] / -0

>12 [305] ≤ 60 [1524] = +.2 [51] / -0

>60 [1524] ≤ 120 [3048] = +.4 [102] / -0

>120 [3048] ≤ 300 [7620] = +.6 [152] / -0

>300 [7620] = +.5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.