

10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax

PE3W13633




Configuration

- Connector 1: 10-32 Male Right Angle
- Connector 2: BNC Female Bulkhead
- Cable Type: RG178
- Coax Flex Type: Flexible

Features

- 70% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W13633 10-32 male right angle to BNC female bulkhead cable using RG178 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 10-32 to BNC cable assembly has a male to female gender configuration with 50 ohm flexible RG178 coax. The right angle 10-32 interface on the RG178 cable allows for easier connections in tight spaces. Our RF cable assembly with BNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.051 lbs [23.13 g]

Cable

Cable Type	RG178
Impedance	50 Ohms
Inner Conductor Type	Stranded

10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax

PE3W13633



Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.072 in [1.83 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	10-32 Male Right Angle	BNC Female Bulkhead
Specification	MIL-C-39012	
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Gold	Phosphor Bronze, Gold
Contact Plating Specification	MIL-G-45204	
Dielectric Type	PTFE	POM
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	QQ-N-290	

Environmental Specifications

Operating Range Temperature	-40 to +85 deg C
-----------------------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax



PE3W13633

Typical Performance Data

How to Order

Part Number Configuration:

PE3W13633

- XX

uu

- Unit of Measure:
cm = Centimeters
<blank> = Inches

- Length

- Base Number

Example: PE3W13633-12 = 12 inches long cable
PE3W13633-100cm = 100 cm long cable

10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax PE3W13633](#)

URL: <https://www.pasternack.com/10-32-male-right-angle-to-bnc-female-bulkhead-cable-using-rg178-pe3w13633-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W13633 CAD Drawing
10-32 Male Right Angle to BNC Female Bulkhead Cable Using RG178 Coax

