

1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02003 Coax in 60 Inch

The 78 ohm TRB 3-Lug jack to Blunt cut genderless 60 inch cable using 78 ohm FMBC-30-02003 twinax, part number FM3MP2442-60, from Fairview Microwave is in-stock and ships same day. This Fairview TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 78 ohm flexible FMBC-30-02003 twinax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FM3MP2442-60 TRB 3-Lug jack to Blunt cut genderless cable assembly operates to 500 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		500	MHz
Capacitance		20.3 [66.6]		pF/ft [pF/m]
Operating Voltage (AC)			300	Vrms

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.174 lbs [78.93 g]

Cable

Cable Type	FMBC-30-02003
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	PVC, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------



Configuration:

- TRB 3-Lug Jack
- Blunt Cut Genderless
- FMBC-30-02003

Features:

- Max Frequency 500 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

Applications:

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Lug Jack Bayonet	Blunt Cut Genderless Other
Impedance	78 Ohms	
Contact Material & Plating	Bronze, Gold 30 micro inches	
Contact Plating Spec.	ASTM-B-488	
Dielectric Type	Teflon	
Outer Cond Material & Plating	Phosphor Bronze, Gold	
Outer Cond Plating Spec.	30 micro inches	
Body Material & Plating	Brass, Nickel	
Body Plating Spec.	ASTM-B-733	

Environmental Specifications

Temperature

Operating Range -20 to +75 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FM3MP2442 - xx uu

cm = Centimeters
 <blank> = Inches

Length


Example: FM3MP2442-12 = 12 inches long cable
 FM3MP2442-100cm = 100 cm long cable

1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02003 Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [1553 TRB 3-Lug Jack to Blunt Cut Genderless Cable 78 Ohm FMBC-30-02003 Coax in 60 Inch FM3MP2442-60](#)

URL: <https://www.fairviewmicrowave.com/1553-trb-3-lug-jack-to-blunt-cut-genderless-cable-78-ohm-fmbc-30-02003-coax-in-60-inch-fm3mp2442-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



LENGTH

BLUNT CUT

LABEL
SEE NOTE 1 & 2

WWW.FAIRVIEWMICROWAVE.COM
FMXXXXXXXXXX

30-02003, 78 OHM TWINAX CABLE
JACKET: PVC, BLUE
NOM. DIA: .150" [3.81]

TRB 3-LUG JACK

SHIELD
WHITE
BLUE

WIRING MAP

NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.

2. CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED: FM3MP2442-XX (-XX = OAL IN INCHES)

3. CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES, DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES

X = ±.2 [5]

XX = ±.02 [0.5]

XXX = ±.005 [0.13]

FRACTIONS

± 1/32

ANGLES ± 1°

CABLE LENGTH TOLERANCES

±12 [305] ≤ 60 [1524] = ±.1 [25] / -0

±6 [152] ≤ 60 [1524] = ±.05 [1.27] / -0

±3 [76] ≤ 60 [1524] = ±.02 [0.51] / -0

±12 [305] ≤ 300 [7620] = ±.1 [25] / -0

±6 [152] ≤ 300 [7620] = ±.05 [1.27] / -0

±3 [76] ≤ 300 [7620] = ±.02 [0.51] / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE

UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION

COLORS MAY VARY

Fairview Microwave®

an INFINIT® brand

Website: www.FairviewMicrowave.com

Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE

NONE

SHEET

1 OF 1

DESCRIPTION

TRB 3-Lug Jack with Blunt Cut for 78 Ohm FMBC-30-02003 Cable

SIZE

A

CAGE CODE

3FKR5

DRAWN BY

KDANG

ITEM NO.

FM3MP2442

REV

A

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 3 of 3

T-Rev D3