



Feature

- 7" 1024 x 600 Wide Viewing Angle LCD
- Quad-core CPU with High Performance Dedicated 3D Processor
- Fan-less Cooling System
- Built-in 4GB Flash Memory and RTC
- COM2 and COM3 RS-485 2W supports MPI 187.5K, please use one at a time
- CAN Bus Supports CANopen, CAN Bus 2.0A/2.0B and SAE J1939
- Built-in Power Isolator
- NEMA4 / IP66 Compliant Front Panel


Display	Display	7" Wide Viewing Angle (WVA)
	Resolution	1024 x 600
	Brightness (cd/m ²)	550
	Contrast Ratio	800:1
	Backlight Type	LED
	Backlight Life Time	>30,000 hrs.
	Colors	16.7M
	LCD Viewing Angle (T/B/R/L)	85/85/85/85
	Pixel Pitch (mm)	0.1506 (H) x 0.1432 (V)
Touch Panel	Type	Tempered Glass, Capacitive Type
	Hardness Scale	7H
Memory	Flash	4 GB
	RAM	1 GB
Processor		Quad-core RISC
I/O Port	SD Card Slot	N/A
	USB Host	USB 2.0 x 1
	USB Client	N/A
	Ethernet	LAN 1: 10/100 Base-T x 1 LAN 2: 10/100 Base-T x 1
	COM Port	Con.A: COM2 RS-485 2W/4W, COM3 RS-485 2W, CAN Bus Con.B: COM1 RS-232 4W, COM3 RS-232 2W ^{*1}
	RS-485 Dual Isolation	N/A
	CAN Bus	Yes
	HDMI	N/A
	Audio Output	N/A
RTC		Built-in
Power	Input Power	24±20%VDC
	Power Isolation	Built-in
	Power Consumption	820mA@24VDC
	Voltage Resistance	500VAC (1 min.)
	Isolation Resistance	Exceed 50MΩ at 500VDC
Specification	PCB Coating	Yes
	Enclosure	Plastic
	Dimensions WxHxD	200.3 x 146.3 x 36.9 mm
	Panel Cutout	192 x 138 mm
	Weight	Approx. 0.7 kg
	Mount	Panel mount
Environment	Protection Structure	UL Type 4X (indoor use only) / NEMA4 / IP66 Compliant Front Panel
	Storage Temperature	-20° ~ 60°C (-4° ~ 140°F)
	Operating Temperature	0° ~ 55°C (32° ~ 131°F)
	Relative Humidity	10% ~ 90% (non-condensing)
	Altitude	3,000 m
	Vibration Endurance	10 to 25Hz (X, Y, Z direction 2G 30 minutes)
Certificate	CE	CE marked
	UL	cULus Listed
Software	EasyBuilder Pro	V6.08.02 or later versions ^{*2}
	Weincloud	EasyAccess 2.0 (Optional), Dashboard (Optional)
	CODESYS®	Optional ^{*3}

^{*1} Only Tx & Rx (no RTS/CTS) may be used for COM1 RS-232 when COM3 RS-232 is also used.

^{*2} The minimum software requirement for units labeled as cMT3072XP (V2): EasyBuilder Pro V6.09.02.

^{*3} CODESYS® is a trademark of CODESYS GmbH.

Dimensions



a	Battery	e	USB Host Port
b	Power Connector	f	LAN 2
c	Con.A: COM2 RS-485 2W/4W, COM3 RS-485 2W, CAN Bus	g	LAN 1
d	Con.B: COM1 RS-232 4W, COM3 RS-232 2W		

Ordering Information

□ cMT3072XP:

7" WVA LCD HMI, 4GB flash memory, 1GB RAM on board

□ RZUSK7010 (included in package)

USB Clamp & Tying Strap

Optional:

□ RZACEA020: EasyAccess 2.0 Activation Card

□ RZ0CDS000: CODESYS License

Pin Assignment:

Con.B: COM1 / COM3 [RS232] 9 Pin, Male, D-sub

PIN#	COM1 [RS232]4W	COM3 [RS232]2W
1		
2	RxD	
3	TxD	
4		
5	GND	
6		
7	RTS	TxD
8	CTS	RxD
9	GND	

Con.A: COM2 / COM3 [RS485] / CAN Bus, 9 Pin, Female, D-sub

PIN#	COM2 [RS485]2W	COM2 [RS485]4W	COM3 [RS485]2W	CAN Bus
1	Data-	Rx-		
2	Data+	Rx+		
3		Tx-		
4		Tx+		
5	GND			
6			Data-	
7				CAN_L
8				CAN_H
9			Data+	