

Extreme Networks 10301 Compatible SFP+ Module - 10GBASE-SR - 10GbE Multimode Fiber MMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 300m - 850nm - DDM

Product ID: 10301-ST



The 10301-ST is an Extreme Networks 10301 compatible fiber transceiver module that has been designed, programmed and tested to work with Extreme Networks brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBASE-SR compliant networks, with a maximum distance of up to 300 m (984 ft).

Technical Specifications:

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 300 m (984 ft)
- MTBF: 498,745,585 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- 100% EXTREME NETWORKS 10301 COMPATIBLE SFP+ TRANSCEIVER: Designed, programmed and tested to work with compatible Extreme Networks switches and routers to deliver reliable 10GbE connectivity
- TECHNICAL SPECS: 10GBASE-SR 10Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 300m (984ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Extreme Networks routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

Hardware

| | |
|--------------------|-------------------------|
| Warranty | Lifetime |
| Compatible Brand | Extreme Networks |
| Industry Standards | IEEE 802.3ae 10GBASE-SR |

Performance

| | |
|----------------------------|--------------|
| Maximum Data Transfer Rate | 10.00 Gbps |
| Max Transfer Distance | 300m [984ft] |
| Type | Multi Mode |
| Wavelength | 850nm |
| Fiber Operating Mode | Full-Duplex |
| DDM | Yes |

| | |
|------------------------------|-------------------|
| Compatible Networks | 10 Gbps |
| MTBF | 498,745,585 hours |
| Power Consumption (In Watts) | < 1.3W |

Connector(s)

| | |
|-------------|---------------------------|
| Connector A | 1 - SFP Slot |
| Connector B | 1 - Fiber Optic LC Duplex |

Power

| | |
|----------------|---------|
| Output Voltage | 3.3V DC |
|----------------|---------|

Physical Characteristics

| | |
|-------------------|-----------------|
| Product Length | 0.5 in [1.4 cm] |
| Product Width | 2.3 in [5.8 cm] |
| Product Height | 0.5 in [1.3 cm] |
| Weight of Product | 0.7 oz [20.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 4.4 in [11.3 cm] |
| Package Width | 3.7 in [9.3 cm] |
| Package Height | 1.3 in [3.3 cm] |
| Shipping (Package) Weight | 1.7 oz [48.0 g] |

What's in the Box

| | |
|---------------------|----------------------|
| Included in Package | 1 - SFP+ Transceiver |
|---------------------|----------------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*