

Brocade 10G-SFPP-SR Compatible SFP+ Module - 10GBASE-SR - 10GbE Multimode Fiber MMF  
Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 200m - 850nm - DDM

**Product ID:** 10G-SFPP-SR-ST



The 10G-SFPP-SR-ST is a Brocade 10G-SFPP-SR compatible fiber transceiver module that has been designed, programmed and tested to work with Brocade brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBASE-SR compliant networks, with a maximum distance of up to 200 m (656 ft).

**Technical Specifications:**

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 200 m (656 ft)
- MTBF: 498,745,585 hours
- Power Consumption: < 1W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

### Features

- 100% BROCADE 10G-SFPP-SR COMPATIBLE SFP+ TRANSCEIVER: Designed, programmed and tested to work with compatible Brocade switches and routers to deliver reliable 10GbE connectivity
- TECHNICAL SPECS: 10GBASE-SR 10Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 200m (656ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Brocade routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Brocade
Industry Standards	IEEE 802.3ae 10GBASE-SR

---

### Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	200m [656ft]
Type	Multi Mode
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
DDM	Yes

---

Compatible Networks	10 Gbps
MTBF	498,745,585 hours
Power Consumption (In Watts)	< 1W

---

**Physical Characteristics**

Product Length	0.5 in [1.4 cm]
Product Width	2.3 in [5.8 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.7 oz [20 g]

---

**Packaging Information**

Package Length	4.4 in [11.3 cm]
Package Width	3.6 in [9.1 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

---

**What's in the Box**

Included in Package	1 - SFP+ Transceiver
---------------------	----------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

