

USB C Video Adapter, USB C to HDMI DVI VGA Adapter, Up to 4K 60Hz, Aluminum, Multiport Video Display Adapter, Thunderbolt 3 / 4 Compatible, USB Type C Travel Adapter

Product ID: 118-USBC-HDMI-VGADVI



This USB-C multiport video adapter offers a durable and portable solution for connecting your USB Type-C device to a n HDMI, DVI, or VGA display.

The HDMI 2.0b output supports up to 4K 60 Hz resolutions and HDR whereas VGA output supports up to 1920x1200 at 60 Hz, and the DVI-I output supports up to 1080p at 60 Hz. All the outputs offer compatibility with older displays supporting lower resolution. The adapter supports dual mirrored 1080p displays when using either VGA and HDMI or VGA and DVI-I monitor configurations.

Avoid the hassle of carrying different adapters with a USB Type-C Multiport Video Adapter. Connect a USB-C DisplayPort Alt-mode device to virtually any display. A durable aluminum enclosure helps the adapter withstand being carried in a travel bag between office, home, shared spaces, and during business travel.

The USB Type-C Display Adapter is compatible with USB-C DisplayPort Alt-mode, Thunderbolt 3, Thunderbolt 4 Laptops, Ultrabooks, Chromebooks, and MacBooks. Plug and Play (PnP) capability allows you to quickly connect to devices running Windows, macOS, iPadOS, chromeOS, or Linux. The VGA and DVI outputs are compatible with screw locking cables ensuring a secure connection with displays and projectors. The 12 inch (30 cm) attached cable allows for flexibility in your setup and less strain on ports and connectors.

118-USBC-HDMI-VGADVI is backed for 3-years by StarTech.com, including free 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility





Applications

- Carry the adapter with you when you travel, and connect to almost any display
- Connect your USB-C device to an HDMI, VGA, or DVI display at an office, home office, in shared spaces, or during business travel
- Connect a secondary VGA, DVI, or HDMI monitor to your MacBook

Features

- **USB-C SINGLE MONITOR ADAPTER:** USB-C DP Alt-mode to HDMI 2.0b (4K 60Hz, 7.1ch Audio, HDR, HDCP 2.2), VGA (1920x1200 60Hz) or DVI-I (1080p 60Hz, HDCP 1.4); This USB C to HDMI DVI VGA Adapter supports dual mirrored video output for VGA & HDMI or VGA & DVI-I
- **4K 60Hz RESOLUTION:** The USB C Video Adapter's HDMI output supports 4K 60Hz and Ultra Wide Screen resolutions up to 3840x1080p 60Hz; Compatible with lower resolutions; Works with monitors and displays from Dell, Asus, Acer, LG, Samsung, Sharp, Sony
- **WIDE HOST COMPATIBILITY:** Compatible with USB-C, Thunderbolt 3 and Thunderbolt 4 Laptops, Ultrabooks and Chromebooks, from HP, Dell, Surface, Lenovo, MacBooks (Intel and M1 chip) The USB C Multiport Video Adapter works on Windows, macOS and Linux
- **TOUGH & PORTABLE:** Durable all aluminium USB Type-C multiport adapter with small form factor is designed for easy transport in a laptop bag; The USB C Video Adapter is convenient for on-the-go use between office, home, shared spaces, and business travel
- **EASY TO USE:** Plug and Play (PnP) installation, no software or drivers required; Extended 12" (30cm) attached cable for setup flexibility; The USB C Adapter is compatible with screw locking cables for secure connection with VGA/DVI displays and projectors

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	VGA
	DVI-I (Digital Only) - Dual-Link
	HDMI

Chipset ID	ITE - IT6224FN
------------	----------------

Performance

Maximum Analog Resolutions	1920 x 1200 @ 60 Hz (VGA)
Maximum Digital Resolutions	3840 x 2160 @ 60 Hz (HDMI) 1920 x 1200 @ 60 Hz (DVI)
Wide Screen Supported	Yes
Audio Specifications	VGA - No Audio Support DVI - No Audio Support HDMI - 7.1 Channel Audio

Connector(s)

Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode
Connector B	1 - VGA (15 pin, High Density D-Sub) 1 - 29 pin DVI-I (Dual Link) Female 1 - HDMI

Software

OS Compatibility	No Drivers or Software Required
------------------	---------------------------------

Special Notes / Requirements

Note	This adapter does not support MST or dual extended displays Support for dual mirrored displays only using combinations of VGA & HDMI or VGA & DVI-I
------	--

Power

Power Source	Bus Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0 to 45 (32F to 113F)
Storage Temperature	-10 to 70 (14F to 158F)

Humidity 10% ~ 85 % RH

Physical Characteristics

Color	Gray
Cable Length	11.8 in [300 mm]
Product Length	3.3 in [8.5 cm]
Product Width	1.8 in [4.5 cm]
Product Height	0.6 in [1.4 cm]
Weight of Product	2.6 oz [75.0 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.5 cm]
Package Width	6.8 in [17.3 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	4.3 oz [122.0 g]

What's in the Box

Included in Package	1 - USB-C Multiport Video Adapter
---------------------	-----------------------------------

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

