

3ft (1m) Power Extension Cord, IEC 320 C14 to NEMA 5-15R, 10A 125V, 18AWG, Black Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/ PDUs / Network Equipment

Product ID: 1415R-3F-POWER-CORD



High-Quality Construction

The universal monitor power cord is built with 18 AWG wire and rated to carry 125V at 10A. It is constructed with fully molded strain relief connectors, ensuring a reliable and durable connection for your devices.

Universal Replacement Cable

This replacement power cord features an IEC 320 C14 to NEMA 5-15R connector and is compatible with most monitors, PCs, scanners, and printers.

Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **AC COMPUTER POWER CABLE:** This 3ft (1m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home offices Indoor use only Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This power extension cord is available in other lengths
- **SPECIFICATIONS:** 3ft (1m) AC Power Cord IEC 60320 C14 to NEMA 5-15R 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 14 to 95F (-10 to 35C) Cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables Extend a 3-prong NEMA 5-15P power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

| | |
|-------------------|----------|
| Warranty | Lifetime |
| Connector Plating | Nickel |

Connector(s)

| | |
|-------------|-------------------------------------|
| Connector A | 1 - IEC 60320 C14 Power |
| Connector B | 1 - NEMA 5-15 Power (North America) |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Wire Gauge | 18 AWG |
| Cable Length | 3.0 ft [0.9 m] |
| Product Length | 1.1 in [2.7 cm] |
| Product Width | 36.0 in [91.5 cm] |
| Product Height | 1.2 in [3.0 cm] |
| Weight of Product | 4.0 oz [114.0 g] |

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|---------------------------|------------------|
| Package Length | 7.4 in [18.7 cm] |
| Package Width | 3.1 in [7.9 cm] |
| Package Height | 1.5 in [3.8 cm] |
| Shipping (Package) Weight | 4.3 oz [122.0 g] |

What's in the Box

| | |
|---------------------|-------------------------|
| Included in Package | 1 - Computer Power Cord |
|---------------------|-------------------------|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

****Product appearance and specifications are subject to change without notice.***

