

Crossbar Dual Monitor Desk Stand For Double 27-inch Screens, VESA Mount 75x75/100x100, Toolless Height Adjustment, Up To 13.2lb (6kg) Per Display

Product ID: 2MC1S-MONITOR-STAND



This crossbar monitor desk stand is designed to support up to two 27-inch displays, creating an ergonomic multi-monitor setup that provides a large viewing area for productivity. Built-in handles enable the height of the monitors to be adjusted simultaneously along the column to suit different ergonomic needs.

The spring-assisted crossbar enables toolless display height adjustment of 9.6 to 15.7in (245-400mm). When the desired height has been achieved, the height adjustment is locked when the paddle lever is released.

The crossbar design of this double monitor mount ensures stable, horizontal alignment of the displays, making it ideal for bezel-less or slim-bezel screens. This helps create an immersive and seamless viewing area. The VESA mounts can slide along the crossbar, allowing greater versatility with visual and ergonomic adjustments.

The monitors' VESA mounts enable +/-45 tilt, +/-40 swivel, & 360 screen rotation for portrait or landscape orientations.

The heavy-duty steel base (7.9x9.4in/200x240mm) features +/-40 swivel motion and can support up to 13.2lb (6kg) per VESA mount.

The freestanding monitor stand includes adhesive cable clips and hook-and-loop straps that help reduce clutter and create a tidy setup. At the bottom of the column a cable pass-through helps to route cables to maintain an organized workspace.

Certifications, Reports and Compatibility

Applications

Features

- **DOUBLE MONITOR DESK STAND:** Dual monitor VESA mount (75x75/100x100) supports up to two 27-inch displays; Crossbar design ensures stable horizontal alignment of monitors at all times for a seamless visual experience; Height-adjustable crossbar along column
- **SYNCHRONIZED HEIGHT ADJUSTMENT:** Top & bottom handles for controlled height adjustment from 9.6 to 15.7in (245-400mm); Toolless adjustments of +/-40 swivel at the base, VESA +/-45 tilt, +/-40 swivel, & 360 screen rotation; Adjust monitor along crossbar
- **DURABLE CONSTRUCTION:** Steel and aluminum construction for durability with a powder-coated finish; Heavy-duty anti-slip desk base for stability (7.9x9.4in/200x240mm); Maximum weight capacity 13.2lb (6kg) per VESA mount
- **HASSLE-FREE INSTALLATION:** VESA plates with keyhole pattern allow easy mounting of a computer monitor for quick setup and deployment; Freestanding mount ships with the necessary tools for assembly
- **CUSTOMIZABLE CABLE MANAGEMENT:** Use the included adhesive cable clips and hook-and-loop cable ties to manage cables; The bottom of the column features a cable pass-through, helping to create a tidy setup; Standing desk mount includes all necessary tools

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	No
# of Displays Supported	2
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Aspect Ratio	16:9

Performance

Weight Capacity (Per Display)	13.2 lb [6 kg]
Minimum Display Size	17"
Maximum Display Size	27"

Fits Curved Display	Yes
Fits UltraWide Displays	No
Height Adjustment	Yes
Minimum Height	9.6 in [245 mm]
Maximum Height	15.7 in [400 mm]
Display Tilt	+ 45 / - 45
Swivel / Pivot	+180 / -180
Display Rotation	360
Anti-theft	No

Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	29.0 in [73.7 cm]
Product Width	7.9 in [20.0 cm]
Product Height	22.4 in [57.0 cm]
Weight of Product	10.0 lb [4.6 kg]

Packaging Information

Package Length	11.3 in [28.6 cm]
Package Width	17.5 in [44.5 cm]
Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	11.8 lb [5.3 kg]

What's in the Box

Included in Package	1 - Monitor Lift Column
	1 - Lift Column Base
	2 - VESA Mount Assembly

- 4 - VESA Mount Caps
- 1 - Lever Back Plate
- 1 - Lever Front Cover
- 2 - Crossbars
- 1 - Crossbar Mount, Upper
- 1 - Crossbar Mount, Lower
- 1 - Grab Handle, Upper
- 1 - Grab Handle, Lower
- 2 - M8 x 20 mm Screws
- 4 - M4 x 6 mm Screws
- 1 - M4 x 8 mm Screw
- 6 - M6 x 12 mm Screws
- 2 - M6 x 15 mm Screws
- 1 - M6 x 40 mm Screw
- 8 - M4 x 12 mm Screws
- 8 - M5 x 12 mm Screws
- 8 - Washers
- 1 - 4 mm Hex Key
- 1 - 5 mm Hex Key With Screwdriver
- 1 - 6 mm Hex Key
- 2 - Adhesive Cable Management Clips
- 4 - Hook and Loop Straps
- 1 - Instruction Manual

**Warranty
Information**

Warranty

5 Years

**Product appearance and specifications are subject to change without notice.*

