

## USB 2.0 Internal Multi-Card Reader / Writer - SD microSD CF - TAA

**Product ID:** 35FCREADBK3



The 35FCREADBK3 3.5" Multimedia Card Reader offers quick and easy access to the most popular flash card formats, from the front panel of almost any desktop computer.

Suitable for quickly accessing memory cards from virtually any portable media device (e.g. digital cameras, MP3 players, etc.), this versatile media card reader supports 22 of the most popular card types, including: Compact Flash (CF type I), Secure Digital (SD/miniSD/microSD/SDHC/SDXC), MultiMediaCard (MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC), MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-RO/MS2), and xD Picture cards, this reader is ready to handle the memory cards from virtually any portable device from cameras to music players.

The card reader also allows simultaneous access to multimedia card types (excluding same type media), allowing you to copy files from or between different cards at the same time.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

## Features

- **USB 2.0 MULTI-CARD READER:** This Internal USB 2.0 Multi-Card Reader fits into any 3.5in drive bay and connects internally to a 9-pin motherboard header; Access the most popular flash card formats from a desktop computer; Includes 9-pin IDC cable and screws
- **WIDE COMPATIBILITY:** Supports CompactFlash type I, SD/miniSD/microSD/SDHC/SDXC, MMC/RS-MMC/HS-MMC/MMCmobile/MMCplus/MMCmicro/HC-MMC, MemoryStick (MS/MS Duo/HS-MS/MS PRO/MS PRO Duo/MS PRO-HG Duo/MS-ROM/M2), and xD Picture card; Front facing USB 2.0 port
- **SIMULTANEOUS SLOT ACCESS:** This internal multi-card reader supports access to multiple media card types simultaneously (excluding same type media), allowing you to conveniently copy files from or between different media cards at the same time
- **CONVENIENT SETUP:** OS independent supporting Windows, macOS, and Linux; Built-in Power and Activity LED; Ideal for saving, editing & transferring content in videography, photography, podcasting, YouTube & social media
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this TAA compliant internal multi-card reader is backed for 2 years, including free lifetime 24/5 multi-lingual assistance

---

### Hardware

Warranty	2 Years
Chipset ID	ITE - 1336

---

### Performance

Max Drive Capacity	Currently tested with up to 256GB microSD cards
Memory Media Type	microSDHC (Micro Secure Digital High Capacity) Mini-SD, Micro-SD (Mini/Micro Secure Digital) SD/MMC (Secure Digital/Multimedia Card) SDHC (Secure Digital High Capacity) SDXC (Secure Digital eXtended Capacity)
	Memory Stick
	M2 (Memory Stick Micro)
	Multi Media Card
	RS-MMC (Reduced Size Multimedia Card)

HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)

HS-MS (High Speed Memory Stick)

MS Duo, MS Pro Duo, MS Pro-HG Duo

xD (Extreme Digital) Picture Card

CF (Compact Flash I Card)

---

**Connector(s)**

Connector Type(s)	1 - IDC (10 pin, Motherboard Header)
External Ports	1 - CompactFlash (50 pin) Slot
	1 - Memory Stick / Memory Stick Pro Slot
	1 - Memory Stick Micro (M2) Slot
	1 - MiniSD / MicroSD / MMC Slot
	1 - SD / MMC Slot
	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - xD-Picture Card Slot

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Special Notes / Requirements**

System and Cable Requirements	Available internal 9-pin USB motherboard header
Note	Simultaneous card access is limited to different media card types

---

**Indicators**

LED Indicators	1 - Power/Activity
----------------	--------------------

---

**Power**

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 125C (-40F to 257F)
Humidity	15-85%

---

**Physical Characteristics**

Color	Black
Material	Steel and Plastic
Product Length	5.1 in [13 cm]
Product Width	4.1 in [10.5 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	7.4 oz [211 g]

---

**Packaging Information**

Package Quantity	1
Package Length	6.4 in [16.2 cm]
Package Width	5.5 in [14 cm]
Package Height	1.4 in [3.6 cm]
Shipping (Package) Weight	9.3 oz [264.0 g]

---

**What's in the Box**

Included in Package	1 - Card Reader
	1 - 9-pin IDC USB cable
	1 - Bag of Mounting Screws
	1 - Instruction Manual

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

