

4m (13ft) LC to LC (UPC) OM4 Multimode Fiber Optic Cable w/Push Pull Tabs, 50/125m, 100G, Bend Insensitive, Low Insertion Loss - LSZH Fiber Jumper Cord

Product ID: 450FBLCLC4PP



LC/UPC to LC/UPC OM4 Multimode Fiber Optic Cable enables 40/100G network connections. The push-pull tabs on each connector ensure quick connection and removal, facilitating accurate installation in high connection density environments. The bend-insensitive fiber and molded strain reliefs support cable runs requiring micro/macro bends while maintaining low attenuation. The retractable strain-relief housings enable toolless in-field polarity swapping. Color-coded LC-Duplex connectors ensure error-free polarity configuration.

Precision-manufactured ceramic ferrules ensure accurate fiber alignment to prevent connectivity issues and minimize insertion loss. Designed for reliability in high-density network applications, the LC to LC UPC polished fiber ends greatly improves return loss characteristics. The Laser-Optimized Multi-Mode Fiber (LOMMF) OM4 fiber patch cable is ideal for 850nm and 1300nm Vertical-Cavity Surface-Emitting Laser (VCSEL) and LED sources.

This multimode 50/125m fiber optic patch cord is backward compatible with OM3 and 1/10/40G networks, ensuring a reliable connection in legacy fiber environments.

Housed in a LSZH (Low-Smoke, Zero-Halogen) flame-retardant jacket, this OM4 fiber cable emits low smoke and toxic fumes when exposed to extreme heat or in the event of a fire. This enables safer cable installations in areas with poor ventilation including some industrial settings, self-contained environments such as trains and aircraft, as well as residential settings where compliance with building codes must be considered.

Each OM4 fiber cable is also individually tested for insertion loss performance that meets or exceeds the TIA/EIA-568 industry standard, for guaranteed compatibility and 100% reliability.

Certifications, Reports and Compatibility



Applications

- Use in 40/100 Gigabit Ethernet and fiber architecture
- Push-pull and toolless polarity swap connectors

Features

- **PUSH-PULL OM4 CABLE:** OM4 LOMMF Cable is immune to EMI and supports up to 100Gbps networks; Push-pull tab design provides easy access for precise insertion/removal in high-density installations; Retractable connector housings for toolless polarity swapping
- **QUALITY CONSTRUCTION:** LC/LC-UPC ends for improved return loss over PC polish; Bend Insensitive fiber core housed in Aramid-reinforced jacket for a loaded bend radius of 6cm and 3cm when unloaded
- **SAFETY AND RELIABILITY:** Individually tested for signal integrity; LSZH (Low-Smoke Zero-Halogen) jacket emits low toxic fumes if combusted; Safe for enclosed/poorly ventilated spaces; Attenuation below 2.4dB/km at 850nm meets or exceeds industry standards
- **WIDE COMPATIBILITY:** OM4 multimode cable supports 10/40/100G networks; Backward compatible with OM3; High micro-bending resistance facilitates tight bends in intricate environments, ideal for fiber switches/servers, SANs, and SFP+/QSFP+/QSFP28 modules
- **SPECS:** 4 meters (13.1ft); OM4; LC/LC UPC; Push Pull Tabs; 50/125m; 850nm or 1300nm LED/VCSEL; Modal Bandwidth: 4700MHz/km (850nm); Attenuation: 2.4dB/km (850nm), 0.6dB/km (1300nm); Cable OD: 2.9mm; Bend Radius: 6cm/2.4in (loaded), 3cm/1.2in (unloaded)

Hardware

Warranty	Lifetime
Fiber Size	50/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM4

Performance

Maximum Data Transfer Rate	100Gbps
Cable Rating	1Gbps / 10Gbps / 40Gbps / 100Gbps
Maximum Cable Length	13.1 ft [4 m]
Type	Multi Mode
Wavelength	850nm

1300nm

Connector(s)

Connector A	1 - Fiber Optic LC Duplex
Connector B	1 - Fiber Optic LC Duplex

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~90% RH

Physical Characteristics

Color	Aqua
Cable Length	13.1 ft [4 m]
Product Length	13.1 ft [4.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.0 in [0.0 mm]
Weight of Product	1.0 oz [29.0 g]

Packaging Information

Package Quantity	1
Package Length	6.3 in [16.1 cm]
Package Width	7.8 in [19.7 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.6 oz [46.0 g]

What's in the Box

Included in Package	1 - 4m OM4 Multimode Fiber Optic Cable LC - LC
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*