

4-Port Industrial USB 3.0 5Gbps Hub, Rugged USB Hub with ESD Protection, DIN/Wall/Desktop Mountable USB-A Hub, USB Expander w/Locking Ports, Heavy Duty - TAA

**Product ID:** 5G4AINDP-USB-A-HUB



Increase USB scalability in industrial environments, product and repair labs, conference rooms or office workstations, using this 4-Port Industrial USB Hub.

This industrial USB hub delivers reliable performance in harsh environments with its heavy-duty, metal housing.

Perfect for factory environments, the rugged hub features ESD protection to each USB port, which aids in preventing damage to any connected devices.

Install the hub where it's best suited for your application. Securely mount the hub to a variety of surfaces, including a wall, desk, or rack, using the built-in mounting brackets and included hardware.

This robust heavy-duty USB 3.0 hub offers four connection ports for connecting USB devices/peripherals.

The industrial USB hub supports 5-24V DC terminal block input, giving you the flexibility to power the hub as required, based on your own power input options.

StarTech.com offers external power adapters, ITB20D3250 and SVA12M5NA, sold separately.

With the optional power adapter, the hub supports USB battery charging specification 1.2, delivering up to 2.4A on any port to a maximum of 30W total, so you can charge your mobile devices faster than traditional USB ports allow.

The hub is OS independent ensuring support on a wide range of platforms including Windows, macOS and Linux.

## Certifications, Reports and Compatibility



## Applications

### Features

- 4-PORT INDUSTRIAL USB HUB: USB 5Gbps expansion hub w/metal enclosure for durability in harsh environments; Provides 4 USB 3.0 Type-A Downstream Facing Ports (DFP); 5Gbps shared; 6ft A-B host cable; USB Event Monitoring utility (available for download)
- ESD PROTECTION: Heavy-duty USB hub with integrated electrostatic discharge safeguards; Protects connected devices with up to 8kV air and 4kV contact ESD protection
- FLEXIBLE MOUNTING OPTIONS: Built-in mounting brackets for wall or desk installation; DIN rail mounting hardware included; Screw-lock connectors on host and device ports to ensure a reliable and secure connection
- POWER OPTIONS: Rugged multiport hub is powered by either the DC barrel connection or terminal block using a 5 to 24V DC source (DC source not incl.); Optional power adapter available ITB20D3250 (sold separately) to power the hub via 2-wire terminal block
- POWER & CHARGE: When connected to a power source, the mountable port expander hub supports BC 1.2 charging; Each port supports 12W (2.4A); Overcurrent protection protects connected devices from overdrawing power

---

### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	4
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB 3.2 Gen 1 (5Gbps)
Chipset ID	VIA/VLI - VL817-Q7

---

**Performance**

Maximum Data Transfer Rate	5 Gbps
Type and Rate	USB 3.2 Gen 1 - 5 Gbit/s
ESD Protection	+/-8kV (Air) +/-4kV (Contact)
MTBF	243,753 Hours

**Connector(s)**

External Ports	4 - USB Type-A (9 pin, 5 Gbps)  1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)  1 - Terminal Block (2 Wire)  1 - Barrel Power Connector (Size M, OD:5.50, ID: 2.10)
----------------	---

**Software**

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

**Special Notes / Requirements**

System and Cable Requirements	Available USB 3.2 Gen 1 Port  USB 3.2 Gen 1 (5 Gbps) is also known as SuperSpeed USB, USB 3.1 Gen 1, and USB 3.0
-------------------------------	--

**Indicators**

LED Indicators	4 - USB Device Connection (Green)  1 - Power (Green)
----------------	--

**Power**

Power Source	Not Included (DC/Terminal Block)
Plug Type	M

**Environmental**

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	5~95% RH

---

**Physical Characteristics**

Color	Black
Form Factor	Industrial
Material	Steel
Cable Length	6.0 ft [1.8 m]
Product Length	7.0 in [17.8 cm]
Product Width	2.3 in [5.9 cm]
Product Height	0.9 in [2.3 cm]
Weight of Product	9.9 oz [280.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.5 in [21.6 cm]
Package Width	5.9 in [15.1 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

---

**What's in the Box**

Included in Package	1 - USB Hub
	1 - 6 ft [1.8 m] USB-A to USB-B Cable
	1 - Terminal Block Connector (Attached)
	1 - DIN Rail Mounting Brackets (with Mounting Screws)
	1 - Quick-Start Guide

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

**\*Product appearance and specifications are subject to change without notice.**