

6ft (1.8m) Power Extension Cord, C14 to C13 PDU Power Cord, 13A 250V, 16AWG, Black
Extension Cable, AC Power Cable for PDU/Power Supply, TAA Compliant, UL Listed

Product ID: 8714-6600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 6 ft

Features

- AC POWER CORD: 6ft (1.83m) 16AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 13A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.83m); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 16AWG; 250V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

Connector(s)

Connector A	1 - IEC 60320 C14 Power
-------------	-------------------------

Connector B 1 - IEC 60320 C13 Power

Power

Input Voltage	250 AC
Input Current	13A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.3 in [8.5 mm]
Product Length	6.0 ft [1.8 m]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	8.5 oz [240.0 g]

Packaging Information

Package Length	7.8 in [19.9 cm]
Package Width	3.0 in [7.6 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	8.8 oz [250.0 g]

What's in the Box

Included in Package	1 - 6ft C14 to C13 Power Cord
---------------------	-------------------------------

Warranty Information

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*

