

6ft (1.8m) Power Cord Splitter, C14 to 2x C13 AC Power Cable, 10A 250V, 18AWG, AC Power Cord Splitter, PC Power Supply Cable, TAA Compliant, UL Listed

Product ID: 8723-8600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Power two workstation devices from a single PDU or wall outlet
- Facilitate two power connections where connectivity is limited

Features

- AC POWER CORD: 6ft (1.83m) 18AWG Computer Power Cord Y Splitter with IEC 60320 C14 to 2x IEC 60320 C13 connectors is suitable for home or office use; Split a single power cord to power two devices or dual monitors; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 6ft (1.83m); TAA Compliant; IEC 60320 C14 to 2x C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 connector works with North American PDUs and power cables; IEC 60320 C13 connector works with most desktop computers, servers, PDUs, printers, and more; PC power splitter cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to 2x C13 power cord Y splitter is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	2 - IEC 60320 C13 Power

Power

Input Voltage 250V AC

Input Current 10A

Output Current 10A

Environmental

Operating Temperature -20 to 105C (-4 to 221F)

Storage Temperature -20 to 105C (-4 to 221F)

Humidity 0% to 65% RH

Physical Characteristics

Color Black

Wire Gauge 18 AWG

Cable Length 6.0 ft [1.8 m]

Cable OD 0.3 in [8.5 mm]

Product Length 6.0 ft [1.8 m]

Product Width 2.0 in [5.1 cm]

Product Height 0.6 in [1.6 cm]

Weight of Product 12.5 oz [354.0 g]

Packaging Information

Package Length 10.2 in [25.8 cm]

Package Width 3.7 in [9.3 cm]

Package Height 1.8 in [4.6 cm]

Shipping (Package) Weight 12.7 oz [360.0 g]

What's in the Box

Included in Package 1 - 6ft C14 Male to 2x C13 Female Splitter Cord

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

