

10ft (3m) Power Extension Cord, PDU Style C14 to Locking C13, PDU Power Cord, 10A 250V, 18AWG, Power Extension Cable, TAA Compliant, UL Listed

Product ID: 87L3-8A00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Locking C13 connector avoids accidental power disconnection
- Extend a monitor, scanner, printer, or PC power cord by an additional 10ft

Features

- AC POWER CORD: 10ft (3.05m) power supply extension cable with IEC 60320 C14 to Locking C13 connector is suitable for workstations or rackmount equipment; Securely connect devices to a PDU or extend a C13 power cable; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; Locking C13 connector prevents accidental disconnection; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 10ft (3.05m); TAA Compliant; IEC 60320 C14 to Locking IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

Power

Input Voltage	250V AC
Input Current	10A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.3 in [7.8 mm]
Product Length	10.0 ft [3.0 m]
Product Width	1.2 in [2.9 cm]
Product Height	0.7 in [1.7 cm]
Weight of Product	10.7 oz [304.0 g]

Packaging Information

Package Length	10.6 in [27.0 cm]
Package Width	3.9 in [9.8 cm]
Package Height	2.4 in [6.1 cm]
Shipping (Package) Weight	11.2 oz [316.0 g]

What's in the Box

Included in Package	1 - 10ft C14 to Locking C13 Power Extension Cord
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***

