

6ft (1.8m) Heavy Duty PDU Power Cord, C14 to C15, 15A 250V, 14AWG, Orange PDU Power Cable, C14 to C15 Heavy Gauge AC Power Cord, TAA Compliant, UL Listed

Product ID: 8915-460Q-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Heavy Duty power cord supports high-powered equipment and PDUs

Features

- **HEAVY DUTY POWER CORD:** 6ft (1.8m) 14AWG Orange Heavy Duty PDU power cord with IEC 60320 C14 to IEC 60320 C15 connector is suitable for servers or high-powered equipment; Indoor use; Rated to carry 250V at 15A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; IEC 60320 C14 to IEC 60320 C15; 14AWG; 250V 15A (Max); Jacket Rating: SJT; Color: Orange; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 connector works with North American PDUs and cables; IEC C15 connector works with most servers, switches, and high-power rackmount appliances; Replacement PDU power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C15 Power

Power

Input Voltage	250V AC
Input Current	15A

	Output Current	15A
Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Orange
	Wire Gauge	14 AWG
	Cable Length	6.0 ft [1.8 m]
	Cable OD	0.3 in [7.8 mm]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.1 in [2.9 cm]
	Product Height	0.8 in [2.1 cm]
	Weight of Product	10.6 oz [300 g]
Packaging Information		
	Package Length	10.5 in [26.6 cm]
	Package Width	3.5 in [9.0 cm]
	Package Height	1.7 in [4.4 cm]
	Shipping (Package) Weight	11.1 oz [314.0 g]
What's in the Box		
	Included in Package	1 - 6ft C14 to C15 Heavy-Duty Power Extension Cord - Orange
Warranty Information		
	Warranty	Lifetime

**Product appearance and specifications are subject to change without notice.*