

120mm Axial Rack Muffin Fan for Server Cabinet, 115V, AC Cooling, Low Noise & Quiet PC Computer Case Fan

**Product ID:** ACFANKIT12



The ACFANKIT12 12cm AC Fan Kit for Server Racks and Cabinets can be installed in StarTech.com's Wall mountable Server Rack Cabinets (RK12WALHM, RK1219WALL and RK1219WALH), as well as many full sized racks from StarTech.com and other manufacturers.

This powerful, yet quiet ball bearing fan will help increase airflow and reduce heat build-up within the cabinet. Capable of moving 107 CFM of air through the rack, this AC powered fan kit is sure to prolong the life of your rackmount equipment.

## Certifications, Reports and Compatibility



## Applications

- Increase airflow, and reduce heat around rack mounted hardware

## Features

- **QUIET VENTILATION:** Increase airflow in your server rack / cabinet to extend equipment life; This 4.7in / 120mm axial rack muffin fan provides low noise (45.7 dbA), AC cooling and is ideal for use with your server, AV and computer equipment
- **POWERED COOLING SYSTEM:** This high performance computer and server rack fan has a standard AC power

connection with included power cord, making it a simple, convenient addition to existing racks or cabinets in your home or office

- **BUILT TO LAST:** Built with a solid metal frame, this fan is 120mm x 38mm and delivers a 107 CFM airflow rate for optimal performance; Operating temperature of 14F to 158F (-10C to 70C), making it ideal for most environments
- **VERSATILE FAN KIT:** Designed to provide airflow and help to reduce heat build-up, this 115V muffin fan is great for computer cases or rack mounted equipment; It comes with the fan, power cord, screws, nuts and washers so you're ready for installation
- **THE IT PRO's CHOICE:** Designed and built for IT Professionals, this rack fan is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	2 Years
Fan Bearing Type	Ball Bearing

---

#### Performance

Air Flow Rate	107 CFM
Noise Level	47.5 dBA
Fan RPM	3050

---

#### Power

Input Voltage	115V AC
Power Consumption (In Watts)	20

---

#### Environmental

Operating Temperature	-10C to 70C (14F to 158F)
-----------------------	---------------------------

---

#### Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.7 in [12 cm]
Product Width	1.5 in [3.8 cm]
Product Height	4.7 in [12 cm]
Weight of Product	20.6 oz [583.8 g]

---

**Packaging  
Information**

Package Quantity	1
Package Length	5.8 in [14.8 cm]
Package Width	7.7 in [19.5 cm]
Package Height	1.9 in [4.8 cm]
Shipping (Package) Weight	1.4 lb [0.6 kg]

---

**What's in the Box**

Included in Package	1 - 120mm x 120mm x 38mm Fan  4 - 8-32 Zinc Plated MachineScrew Nut  4 - 8-32 x 2" Phillips Pan HeadZinc Plated Machine ScrewBulk  4 - #8 Zinc Plated Split LockWasher  1 - AC Power Cord
---------------------	---

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

