

1U Adjustable Vented Server Rack Mount Shelf - 175lbs - 19.5 to 38in Adjustable Mounting Depth  
Universal Tray for 19" AV/ Network Equipment Rack - 27.5in Deep - TAA

**Product ID:** ADJSHELF



The ADJSHELF Adjustable Mounting Depth Rack Mount Shelf offers a simple way to effectively organize mission critical computer hardware in your server racks and cabinets.

Compatible with all 19in (wide) server racks/cabinets, the fixed rack shelf can be adjusted from 19in to 38in (mount depth) as necessary. A sturdy cold-rolled steel construction provides long term durability and enables a weight capacity of up to 175 lbs (80 kg).

Backed by a StarTech.com 2-year warranty.

## Certifications, Reports and Compatibility



## Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware.

## Features

- **UNIVERSAL 19" FIT:** This vented server rack mount shelf is designed to fit any 19in server rack and has a fixed surface depth of 27.56in (70cm), and an adjustable mounting depth range of 19.5-38in (50-97cm) for your data,

networking or other equipment

- **MAXIMIZE VENTILIATION:** The vented shelf ensures consistent airflow to effectively dissipate heat on servers; It also works great to keep your computer and AV equipment cool
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy IT-grade cabinet shelf ensures long term durability and supports a total weight load of 175lb (80kg)
- **VERSATILE FUNCTIONALITY:** With a surface depth of 27.56in (70cm) and adjustable mounting depth range of 19.5-38in, this shelf can work with any 19in cabinet or equipment rack. It provides additional storage space for your tools or A/V accessories.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

|                  |          |
|------------------|----------|
| Warranty         | Lifetime |
| U Height         | 1U       |
| Cable Management | No       |

---

#### Performance

|                                 |                  |
|---------------------------------|------------------|
| Weight Capacity<br>(Stationary) | 176.4 lb [80 kg] |
|---------------------------------|------------------|

---

#### Special Notes / Requirements

|      |                              |
|------|------------------------------|
| Note | Depth adjustable from 19-38" |
|------|------------------------------|

---

#### Physical Characteristics

|                        |                   |
|------------------------|-------------------|
| Color                  | Black             |
| Internal Width         | 17.6 in [44.6 cm] |
| Internal Height        | 1.6 in [40 mm]    |
| Internal Depth         | 27.6 in [70 cm]   |
| Product Length         | 38.3 in [97.4 cm] |
| Product Width          | 17.5 in [44.5 cm] |
| Product Height         | 1.6 in [4.0 cm]   |
| Weight of Product      | 9.7 lb [4.4 kg]   |
| Maximum Mounting Depth | 38.3 in [97.4 cm] |

Minimum Mounting Depth 19.5 in [49.5 cm]

---

#### Packaging Information

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 19.7 in [50.1 cm] |
| Package Width             | 32.4 in [82.3 cm] |
| Package Height            | 2.9 in [7.3 cm]   |
| Shipping (Package) Weight | 12.6 lb [5.7 kg]  |

---

#### What's in the Box

|                     |                             |
|---------------------|-----------------------------|
| Included in Package | 1 - slotted fixed shelf     |
|                     | 2 - front mounting brackets |
|                     | 2 - rear mounting brackets  |
|                     | 8 - M5 screws               |
|                     | 8 - M5 cage nuts            |
|                     | 8 - M5 flanged lock nuts    |
|                     | 8 - M5 truss head screws    |
|                     | 1 - instruction manual      |

---

#### Warranty Information

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

*\*Product appearance and specifications are subject to change without notice.*