

1U 4-Post Adjustable Server Rack Mount Shelf - 330lbs(150 kg) - 19.5 to 38in Adjustable Mounting Depth Universal Tray for 19" AV, Data & Network Equipment Rack - 27.5in Deep

Product ID: ADJSHELFHD



The ADJSHELFHD 1U 4-post Adjustable Heavy Duty Fixed Rack Mount Shelf lets you add a high-capacity, adjustable 1U shelf to virtually any standard 4-post 19-inch server rack or cabinet.

This heavy duty rackmount shelf can be adjusted from 19.5in to 38in (mounting depth) to fit your rack. Constructed using 1.0mm SPCC commercial grade cold-rolled steel, providing the ability to hold up to 150kg (330lbs) of equipment - a durable solution for storing large, non-rackmount pieces of equipment, heavy tools or peripherals in your rack or cabinet.

The ADJSHELFHD is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

- Supply additional storage space for heavy, mission critical hardware and non-rack mount equipment
- For use with all 19" wide Server Racks and Cabinets

Features

- **UNIVERSAL 19" FIT:** This server rack mount shelf is designed to fit any 19in 4-post server rack and has a fixed

surface depth of 27.56in, and an adjustable mounting depth range of 19.5-38in for your data, networking or other small-form tools / equipment

- **COMPACT DESIGN:** The adjustable rack shelf features a very compact form factor, making it ideal for non-rackmount equipment, tools and peripherals in your home, studio or office space
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy IT-grade cabinet shelf ensures long term durability and supports a total weight load of 330 lb / 150 kg
- **VERSATILE FUNCTIONALITY:** With a surface depth of 27.56in and adjustable mounting depth range of 19.5-38in, this shelf can work with any 19 inch cabinet or equipment rack; It provides additional storage space for your tools or A/V accessories
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	1U
Cable Management	No
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front and Rear)

Performance

Weight Capacity (Stationary)	330.8 lb [150 kg]
General Specifications	Weight Capacity: Rev 01 - up to 175lbs / 80kg; Rev 02 or above - up to 330lbs / 150kg

Physical Characteristics

Color	Black
Material	Steel
Rail Thickness	0.0 in [1.0 mm]
Product Length	27.6 in [70.0 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.4 cm]

Weight of Product 13.7 lb [6.2 kg]

Maximum Mounting Depth 38.3 in [97.4 cm]

Minimum Mounting Depth 19.5 in [49.5 cm]

Packaging Information

Package Quantity	1
Package Length	21.2 in [53.8 cm]
Package Width	30.1 in [76.4 cm]
Package Height	4.4 in [11.3 cm]
Shipping (Package) Weight	16.0 lb [7.3 kg]

What's in the Box

Included in Package	1 - 1U High Cap Adjustable Rack Shelf
	1 - Instruction Manual
	1 - 1U Shelf Body
	2 - Front Mounting Brackets
	2 - Rear Mounting Brackets
	8 - M6x12 mm Screws
	8 - M6 Cage Nuts
	8 - M6 Plastic Washer
	8 - M6x12mm Mounting Bracket Screws

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*