

Dual-Monitor Stand - Horizontal - Black - For up to 24" (17.6lb/8kg) Displays

**Product ID:** ARMBARDUO



Increase your productivity and free up desk space with this dual-monitor stand. The free-standing mount lets you install two displays up to 24", side by side, on a single base that you can place in virtually any workspace. The black finish complements your office decor.

Set up a dual-monitor workstation with this VESA monitor stand (75x75, 100x100 mm) to multitask faster and boost your productivity. Compare and edit files on two screens with ease. Rotate your monitors 360 degrees for portrait or landscape viewing.

Maximize the surface area on your desk with the twin-monitor stand. Its crossbar design makes it easy to mount two flat-panel displays. The monitor stand features a flat, low-profile back so you can position your displays against an office wall or cubicle wall to free up space.

The crossbar design of the dual-monitor stand keeps your monitors perfectly aligned for comfortable viewing. You can customize the positioning of your displays with +/-15 degree tilt. You can also adjust the height of the monitors along the pole, up to 15.9" (40.5 cm).

The robust steel and aluminum monitor stand provides a stable setup for your workstation. The sturdy platform also allows flexible use as a temporary setup, for example, to make presentations in the boardroom.

ARMBARDUO is backed by a 5-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Add two monitors to your work station to complete your tasks quicker
- Maximize desk space by mounting both of your monitors on a single base
- Low-profile base with attractive black finish works well in offices or cubicles

## Features

- Enhance productivity and free up space by mounting two monitors up to 24"
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 26.3"/66.8 cm)
- Free-standing monitor stand with crossbar design keeps monitors aligned
- Easy height adjustment along the pole, and +/-15 degree tilt for customized viewing
- Steel and aluminum stand supports VESA 75x75, 100x100, and a weight capacity of 18 lb. (8 kg) per monitor

---

### Hardware

Warranty	5 Years
Wallmountable	No
Articulating	No
# of Displays Supported	2
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

---

### Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Maximum Display Size	24"
Height Adjustment	Yes
Maximum Height	15.9 in [405 mm]
Display Tilt	+/-15
Swivel / Pivot	360 at each display

---

**Physical Characteristics**

Color	Black
Material	Steel, Aluminum and Plastic
Product Length	37.4 in [95 cm]
Product Width	7.1 in [18 cm]
Product Height	16.1 in [41 cm]
Weight of Product	13.6 lb [6.2 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	12.2 in [31.1 cm]
Package Width	28.6 in [72.6 cm]
Package Height	4.9 in [12.5 cm]
Shipping (Package) Weight	16.1 lb [7.3 kg]

---

**What's in the Box**

Included in Package	1 - pole
	1 - baseplate
	3 - M6x15 screws
	1 - cable-management clip (pole)
	1 - pole cap
	1 - height-adjustment ring
	1 - crossbar
	2 - VESA monitor mounts
	8 - M4x12 screws
	8 - M4x30 screws
	8 - plastic spacers

1 - allen wrench (3mm)

1 - allen wrench (4mm)

2 - cable-management clips (crossbar)

1 - instruction manual

---

**Warranty  
Information**

Warranty	5 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*