

Desk-mount Dual-Monitor Arm - Cross Bar - Grommet/Desk Clamp Mount - For up to 27" (17.6lb/8kg) Displays

Product ID: ARMBARDUOG



This deskmount dual-monitor arm lets you mount two 13" to 27" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable dual-arm design, the double-monitor mount lets you create more usable work space by mounting your monitors side by side on a single base. The screen mount features a flat low-profile back that lets you position your displays against a wall or cubicle wall.

The computer monitor desk mount features adjustable height along the pole. The smooth +/- 30° tilt motion and +/- 30° swivel make it easy to find the optimal viewing angle. You can also rotate your display 360° for portrait or landscape viewing, and make sure your displays are perfectly aligned using the micro-adjustment knob.

The dual-monitor arm is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

Adding two monitors gives you the extra screen space you need to simplify multitasking and maximize your productivity.

ARMBARDUOG is backed by a 5-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount two monitors on a single base to save desk space
- Maximize office space, creating a dual-monitor workstation against a wall or cubicle wall
- Works with sit-stand workstations, using the desk clamp or grommet mount

Features

- Save space by mounting two monitors up to 27" onto a single base (max. weight 17.6 lb. / 8 kg)
- Landscape-to-portrait display rotation (for use in portrait position, the mount supports ultrawide displays with max width of 23"/58.4 cm)
- Work comfortably with adjustable height, +/- 30°tilt, +/- 30°swivel and 360° rotation
- Versatile use with desk-clamp or grommet-hole mounting
- Place monitors close to a wall/cubicle wall, with a low-profile design

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	No
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

Performance

General Specifications	Pole Height: 14.2" (360 mm)
	Dual-Arm Span: 32.87" (835 mm)
Weight Capacity (Per)	17.6 lb [8 kg]

Display)

Minimum Display Size	13"
Maximum Display Size	27"
Height Adjustment	Yes
Maximum Height	14.3 in [364 mm]
Display Tilt	+ 30 / - 30
Swivel / Pivot	+30/ -30
Display Rotation	360

Physical Characteristics

Color	Black
Material	Steel, Aluminum and Plastic
Product Length	34.3 in [87.0 cm]
Product Width	5.3 in [13.5 cm]
Product Height	20.3 in [51.5 cm]
Weight of Product	10.8 lb [4.9 kg]

Packaging Information

Package Quantity	1
Package Length	10.1 in [25.6 cm]
Package Width	18.9 in [48.0 cm]
Package Height	4.8 in [12.3 cm]
Shipping (Package) Weight	12.3 lb [5.6 kg]

What's in the Box

Included in Package	1 - Column
	2 - VESA Adapters
	2 - Cable-Management Clips (Column)

- 2 - Monitor Arms
- 2 - End Caps
- 2 - Cable-Management Clips (Monitor Arm)
- 2 - End-Cap Screws
- 1 - Desk-Mount Clamp
- 1 - Hex Key
- 1 - Hex Key Screwdriver
- 8 - M4x14 Screws
- 8 - M5x14 Screws
- 8 - Flat Washers
- 1 - Grommet-Mounting Adapter
- 1 - Grommet-Mount Plate
- 5 - Rubber Pads
- 1 - Instruction Manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*