

Dual-Monitor Stand, Vertical - For up to two 27" or 34" Ultrawide (22lb/10kg) VESA Mount Displays

Product ID: ARMBARDUOV



This sturdy and sleek dual-monitor stand raises two displays off the surface of your desk or table, to save space while increasing your productivity. With its steel construction, the freestanding monitor stand securely holds two monitors, each up to 27", or two ultrawide monitors up to 34", stacked vertically.

The dual-monitor stand holds two displays, one above the other, in a vertical configuration. You can work more comfortably, reducing neck and eye strain without having to look side to side when comparing files or reviewing reference material on your screens. It's ideal for numerous applications including web design, coding, creating and reviewing files, and many others. The monitor mount saves valuable desk space and lets you work clutter-free, which is a welcome addition in numerous office environments including business, healthcare and financial settings. You can adjust the height of the monitors as needed, along the 32.2" (818 mm) pole.

The monitor stand enables smooth, effortless +45/-45 tilt and +45/-45 swivel, making it easy to reduce glare and find the perfect viewing angle. It can also rotate a full 360 giving you the flexibility of portrait or landscape viewing.

The heavy-duty steel monitor stand holds your monitors securely in place, to protect your investment and provide long-lasting stability. The dual-monitor stand supports two displays 13" to 27" each in size, or ultrawide monitors up to 34", with a maximum weight of 22.1 lb. (10 kg) per monitor. The surface finish features a powder coating to help resist scratches.

For easier mounting, the VESA mount features notches that let you pre-set the mounting screw, then slide the monitor into place and tighten the screw. To help keep your work area free of clutter, the monitor stand also features cable clips that keep your cables neatly out of sight.

The ARMBARDUOV is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Stack your displays one on top of the other, ideal for web design or coding
- Increase your comfort when working on two screens to create files or compare documents
- Enhance your productivity in office settings including business, healthcare, financial and real estate
- Save space in your home office

Features

- Mount two monitors vertically to save space and increase your comfort
- Freestanding monitor stand supports two displays up to 27", or ultrawide displays up to 34", and 22.1 lb. (10 kg) in weight per monitor
- Heavy-duty steel construction
- The height of the monitors can be adjusted along the 32.2" (818 mm) pole
- Adjust your screen angle easily with +45/-45 tilt and +45/-45 swivel
- Full 360 rotation
- Cable management

Hardware

Warranty	5 Years
Wallmountable	No
Articulating	No
# of Displays Supported	2
Orientation	Vertical
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

Performance

Weight Capacity (Per Display)	22.0 lb [10 kg]
Minimum Display Size	13"
Maximum Display Size	27"
Fits UltraWide Displays	Yes
Display Tilt	+ 45 / - 45
Swivel / Pivot	+45 / -45
Display Rotation	360

Physical Characteristics

Color	Black
Material	Steel
Product Length	12.4 in [31.6 cm]
Product Width	17.1 in [43.4 cm]
Product Height	32.2 in [81.8 cm]
Weight of Product	8.8 lb [4.0 kg]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	18.1 in [46.1 cm]
Package Height	4.4 in [11.3 cm]
Shipping (Package) Weight	9.9 lb [4.5 kg]

What's in the Box

Included in Package	1 - lower pole
	1 - upper pole
	1 - baseplate

- 2 - VESA monitor mounts
- 1 - pole connector
- 2 - cable-management clips
- 1 - cap
- 1 - 3 mm hex key
- 1 - 5 mm hex key
- 1 - 6 mm hex key
- 8 - M4x12 mm screws
- 8 - M5x12 mm screws
- 8 - washers
- 1 - instruction manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

