

Desk-Mount Dual Monitor Arm - Full Motion Articulating - Premium - For up to 30" (19.8lb/9kg) Displays - TAA

Product ID: ARMDUAL30



Customize your workspace like never before with this premium desk-mount dual monitor arm. It supports two VESA (75x75, 100x100) monitors, side-by-side or stacked. The full-motion articulating arms with spring-assisted height adjustment let you reposition your monitors with ease.

Create a dual-monitor setup to suit your needs, using the interchangeable arms with quick-connect assembly.

In a horizontal setup, the dual-monitor mount supports two monitors from 12" to 30". It's ideal for numerous uses including graphic design, photo editing and many others.

As a vertical monitor stand, the dual-monitor arm supports two monitors from 12" to 24". A stacked setup makes it easy to compare information on two screens without scrolling. Please note: To support two stacked 24" monitors, the height of each monitor (including the bezel around the display) cannot exceed 14" (35 cm).

The adjustable dual monitor arm offers a full range of motion on several axes, letting you tilt, pan and rotate. Switch from landscape to portrait viewing.

Raise or lower your monitors with one smooth motion, using the spring-assisted height adjustment. Adjust the tension to your own preference.

With its steel and aluminum construction, the dual monitor mount supports a weight capacity of 19.8 lb. (9 kg) per arm.

The quick slide-and-click connections make the dual-monitor mount easy to assemble. Clamp the monitor mount to the side of your desk or table (using the pre-installed desk clamp) or attach it through a grommet hole.

The TAA compliant ARMDUAL30 is backed by a 10-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Improve workstation ergonomics in commercial, business and home-office environments
- Use a dual-monitor setup for customer service, web design, financial analysis and other uses
- Mount your displays to your desk or table, using the desk clamp or grommet hole mount

Features

- HEAVY-DUTY DUAL MONITOR MOUNT: VESA 75x75/100x100mm compatible desk mount dual monitor arm supports two displays up to 30" (16:9) 19.8lb/9kg each; Full motion articulation, aluminum & silver finish; Mount displays side by side or max 24" (16:9) stacked
- SPACIOUS AND ORGANIZED WORKSPACE: Space-saving design enhances the work area with built-in adjustable cable management along the arms and center pole. Tighten c-clamp (0.78-3.93" thick) or grommet mount (0.39-2.36" thick) by hand to easily secure to desk
- MECHANICAL SPRING ONE-TOUCH ADJUSTMENT: The full motion arms are designed with mechanical springs of the highest quality that have passed a 10,000 cycle test and are covered by a 10-year warranty. The monitor mount is also TAA compliant
- EASY INSTALLATION: Premium dual monitor arm with toolless slide & click design makes assembling easy; Pre-assembled desk clamp & pole that is easily secured by hand to the desk. Independent arms for vertically stacked/side by side monitors
- WIDE RANGE OF MOTION: Ergonomic and full-motion w/ independent toolless 10.7"/270mm adjustable height; Max height from the desk 28.4"/721mm; The arms extend from the pole 26.54"/674mm; +90/-15 tilt, +/-90 swivel, +/-90 rotation (landscape/portrait)

Hardware

Warranty	10 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

Mounting Surface Thickness	Desk Clamp: Table Thickness 0.78 - 3.93 in. (20 - 100 mm) Grommet Clamp: Table Thickness 0.78 - 1.96 in. (20 - 50 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm)
----------------------------	---

Performance

Weight Capacity (Per Display)	19.8 lb [9 kg]
Maximum Display Size	30in
Height Adjustment	Yes
Minimum Height	7.9 in [200 mm]
Maximum Height	28.9 in [735 mm]
Maximum Arm Extension	23.2 in [590 mm]
Swivel / Pivot	360 around the support post 180 at the shoulder 360 at the elbow
Display Rotation	360

Physical Characteristics

Color	Silver & Black
Material	Steel, Aluminum and Plastic
Product Length	18.7 in [476.0 mm]
Product Width	24.3 in [61.8 cm]
Product Height	17.8 in [45.1 cm]
Weight of Product	14.0 lb [6.3 kg]

Packaging Information

Package Quantity	1
Package Length	15.6 in [39.6 cm]
Package Width	21.0 in [53.4 cm]

Package Height 5.6 in [14.1 cm]

Shipping (Package) Weight 17.0 lb [7.7 kg]

What's in the Box

Included in Package	1 - 2-in-1 desk or grommet mount
	2 - M6 Allen key
	2 - M3 Allen key
	1 - base cushion
	2 - spring arms
	2 - swivel arms
	2 - VESA monitor mounts
	8 - thumb screws
	2 - quick release cable managers
	1 - dual mount
	1 - instruction manual

Warranty Information

Warranty	10 Years
----------	----------

**Product appearance and specifications are subject to change without notice.*