

Dual Monitor Stand - Ergonomic Free Standing Dual Monitor Desktop Stand for two 24" (17.6lb/8kg)  
VESA Mount Displays - Synchronized Height Adjustable - Double Monitor Pole Mount - Silver

**Product ID:** ARMDUOSS



Increase your productivity and free up desk space with this dual-monitor stand. The free-standing mount lets you install two displays up to 24", side by side, on a single base that you can place in virtually any workspace. The silver finish adds a designer touch to your office decor.

Set up a dual-monitor workstation with this VESA monitor stand (75x75, 100x100 mm) to boost your productivity. Compare and edit files on two screens with ease. Rotate your monitors 360 degrees for portrait or landscape viewing.

Maximize the surface area on your desk with the twin monitor stand. Its crossbar design makes it easy to mount two flat-panel displays. The monitor stand features a low-profile flat back so you can position your displays against an office wall or cubicle wall to free up space.

The crossbar design of the dual-monitor stand keeps your monitors perfectly aligned for comfortable viewing. You can customize the positioning of your displays with +/-15 degree tilt. You can also adjust the height of the monitors along the pole, up to 15.9" (40.5 cm).

The robust steel and aluminum monitor stand provides a stable set-up for your workstation. The sturdy platform also allows flexible use as a temporary setup, for instance, to make presentations in the boardroom.

ARMDUOSS is backed by a 5-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Add two monitors to your workstation to complete your tasks quicker
- Maximize desk space by mounting both of your monitors on a single base
- Low-profile base with attractive silver finish works well in offices or cubicles

## Features

- DUAL 24 INCH MONITOR MOUNT: VESA 75x75/100x100mm compatible heavy duty freestanding dual monitor desktop stand supports two displays up to 24" (18lb/8kg) per screen; Features a stylish silver finish
- HEIGHT ADJUSTABLE CROSSBAR DESIGN: Secure 2 monitors along the 25.2" horizontal crossbar with rotation & height adjustment (by hand w/ the lever) along the 15.9" (404mm) pole
- WIDE RANGE OF MOTION: Ergonomic monitor positioning w/ ball joint design for ideal viewing angles; +/-15 tilt and 360 rotation (portrait/landscape); Align monitors w/ micro height adjustment
- STABLE & NON-SLIP: Aluminum free standing monitor mount w/ low profile base (10.9" (278mm) x 17.7" (450mm)) for max stability & flexible placement; Anti-slip rubber pads prevent scratches on surfaces
- ORGANIZED WORKSPACE: Double monitor universal VESA mount for computer/PC with cable management clips along the silver arms & center pole to organize cables for a tidy setup

---

### Hardware

|                         |               |
|-------------------------|---------------|
| Warranty                | 5 Years       |
| Wallmountable           | No            |
| Articulating            | No            |
| # of Displays Supported | 2             |
| Mounting Options        | Desktop Stand |
| VESA Hole Pattern(s)    | 75x75 mm      |
|                         | 100x100 mm    |

---

### Performance

|                               |                  |
|-------------------------------|------------------|
| Weight Capacity (Per Display) | 17.6 lb [8 kg]   |
| Maximum Display Size          | 24"              |
| Height Adjustment             | Yes              |
| Maximum Height                | 15.9 in [405 mm] |

Display Tilt      +/-15

Display Rotation      360

---

**Physical Characteristics**

|                   |                             |
|-------------------|-----------------------------|
| Color             | Silver                      |
| Material          | Steel, Aluminum and Plastic |
| Product Length    | 7.1 in [18.0 cm]            |
| Product Width     | 37.4 in [95.0 cm]           |
| Product Height    | 16.1 in [41.0 cm]           |
| Weight of Product | 257.0 oz [7280.0 g]         |

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 28.6 in [72.6 cm] |
| Package Width             | 12.0 in [30.5 cm] |
| Package Height            | 4.7 in [12.0 cm]  |
| Shipping (Package) Weight | 16.4 lb [7.4 kg]  |

---

**What's in the Box**

|                     |                                  |
|---------------------|----------------------------------|
| Included in Package | 1 - Pole                         |
|                     | 1 - Baseplate                    |
|                     | 3 - M6x15 mm Screws              |
|                     | 1 - Cable-Management Clip (Pole) |
|                     | 1 - Pole Cap                     |
|                     | 1 - Height-Adjustment Ring       |
|                     | 1 - Crossbar                     |
|                     | 2 - VESA Mounts                  |
|                     | 8 - M4x12 mm Screws              |

8 - M4x30 mm Screws

8 - Plastic Spacers

1 - M3 Hex Key

1 - M4 Hex Key

1 - M5 Hex Key

2 - Cable-Management Clips (Crossbar)

1 - Instruction Manual

---

**Warranty  
Information**

|          |         |
|----------|---------|
| Warranty | 5 Years |
|----------|---------|

---

*\*Product appearance and specifications are subject to change without notice.*