

Single Monitor Stand - Adjustable - Steel - Silver - For up to 34" (30.9lb/14kg) Displays - TAA

Product ID: ARMPIVSTND



This robust steel single monitor stand, with its sleek silver finish, provides secure support for your display and makes an attractive addition to your workspace. The monitor desk stand allows flexible placement of your computer screen, and is easily adjustable for ideal viewing.

The monitor mount holds your display with ease, supporting monitors from 12" to 34" up to a maximum weight capacity of 30 lb. (14kg).

For added flexibility, you can use the included hardware to mount your Apple Cinema Display, Thunderbolt Display or Apple iMac. The stand works with any Apple Cinema Display or Thunderbolt Display that came with a removable stand or built-in VESA mount adapter. It also works with the 24-inch iMac and 27-inch iMac with a removable stand, or with a built-in VESA mount adapter.

The monitor desk stand features a 15" (380 mm) tall support post, providing a wide range of height adjustment for greater comfort while you work. Adjust your display height, position and viewing angles easily to create an ergonomic work environment.

The adjustable monitor stand lets you mount a display on the desk stand, with tilt and swivel adjustments for ideal positioning. For viewing longer pages or blocks of code without scrolling, the desk monitor stand also supports landscape-to-portrait display rotation.

Made of durable steel, the single monitor mount provides easy set-up for a wide range of monitors. The integrated cable management helps to keep your cables organized and out of view.

The TAA compliant ARMPIVSTND is backed by a StarTech.com 10-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount a display on your desk, table or counter with tilt, swivel and height adjustment capabilities
- Rotate your display to portrait orientation for web design and coding

Features

- **EASE OF INSTALLATION:** This single monitor stand features a detachable VESA mount to facilitate the actual mounting of the display; It also features cable management system
- **SUPPORTS VESA COMPATIBLE DISPLAYS:** Ensuring ultimate compatibility, the single computer screen monitor stand supports flat or curved (up to 34") or ultrawide (up to 27") VESA mount monitors
- **EASY TO USE:** With a height adjustment up to 15" the premium monitor mount stand can rotate your displays 360 deg. for portrait/landscape viewing, has a +40/-15 tilt and 360 deg. swivel
- **HEAVY-DUTY STEEL CONSTRUCTION:** The single monitor desk stand securely supports a VESA mount monitor (75x75, 100x100 mm) with a maximum weight capacity of 30lb / 14kg
- **ORGANIZED WORKSPACE:** TAA compliant monitor stand with integrated cable management system to organize cables for a tidy setup

Hardware

Warranty	10 Years
Wallmountable	No
Cable Management	Yes
Articulating	No
# of Displays Supported	1
Mounting Options	Desktop Stand
VESA Hole Pattern(s)	75x75 mm
	100x100 mm

Performance

General Specifications ARMPIVSTND is compatible with:

- 24-inch LED Cinema Display and 27-inch LED Cinema Display
- 27-inch Apple Thunderbolt Display
- 24-inch iMac and 27-inch iMac with removable stand or built-in VESA mount adapter

Weight Capacity (Per Display) 30.9 lb [14 kg]

Maximum Display Size 34"

Fits Curved Display Yes

Fits UltraWide Displays Yes

Height Adjustment Yes

Display Tilt +45 / -15

Display Swivel 60

Display Rotation 360

Special Notes / Requirements

Note This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 30.9 lb. (14 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 27" (68.5 cm).

Environmental

Operating Temperature 0C to 50C (32F to 122F) - Indoor Use Recommended

Storage Temperature -20C to 60C (-4F to 140F)

Humidity Operating Humidity 20%~80% HR, non-condensing

Storage Humidity 10%~85% RH, non-condensing

Physical Characteristics

Color Silver

Material Steel and Aluminum

Product Length 10.2 in [26.0 cm]

Product Width 13.0 in [33.0 cm]

Product Height 4.1 in [10.5 cm]

Weight of Product 5.2 lb [2.4 kg]

Packaging Information

Package Quantity 1

Package Length 11.2 in [28.4 cm]

Package Width 21.3 in [54.1 cm]

Package Height 4.8 in [12.1 cm]

Shipping (Package) Weight 7.1 lb [3.2 kg]

What's in the Box

Included in Package 1 - Aluminum Base

1 - Support Post

1 - Monitor Mount

1 - Cable Clip

1 - Iron Position Ring

4 - M5x18mm Hex Screws

1 - Flange

4 - Plastic Caps

1 - Torx Tool

1 - 3mm Allen Wrench

1 - 4mm Allen Wrench

1 - Access Card

4 - Thumb Screws

2 - M6x16mm Screws

4 - Rubber Feet

1 - Instruction manual

**Warranty
Information**

Warranty	10 Years
----------	----------

**Product appearance and specifications are subject to change without notice.*

