

Desk Mount Dual Monitor Arm with USB & Audio, Desk Clamp VESA Mount for up to 32" (17.6lb/8kg) Displays, Ergonomic Full Motion Dual Monitor Arm - Black

**Product ID:** ARMSLIMDUO



Enhance productivity and free up valuable space with the ARMSLIMDUO Dual-Monitor Arm. Two independent arms make it easy to adjust your dual-monitor setup, plus two USB pass-through ports and headset plugs provide easy accessibility to ports.

When you mount your displays on a dual-monitor arm above your desk or table surface, you can adjust your display height, position and viewing angles easily to create a more comfortable and ergonomic work environment. You also get the added benefit of reclaiming valuable workspace by clearing monitor stands off your desk, plus the cable management system keeps cables neatly tucked away.

The dual-arm monitor mount holds two 12" to 32" monitors, side-by-side, with ease. Each arm supports up to 8.0 kg (17.6 lb.) of weight.

The ARMSLIMDUO gives you easy access to two USB pass-through ports and two audio ports located at the front of the base. The ports let you conveniently extend the ports on your PC or laptop, using the integrated cables. This lets you plug in your microphone, headset or USB devices, without having to reach around to access the ports on your computer. It also gives you a cleaner cable setup, which adds to a more productive, less cluttered work space.

The desk-mount monitor arms offer a full range of motion on several axes, letting you tilt, pan and rotate your monitors to adjust your viewing angle any time to suit your changing needs. To view longer pages or blocks of code without scrolling, the arms also support landscape-to-portrait display rotation for each monitor.

The spring-assisted height adjustment makes raising or lowering your monitors effortless. You can also adjust the tension to your own preference.

With its durable aluminum construction, the ARMSLIMDUO securely holds two monitors using a standard VESA mount. The C-clamp makes it easy to install the dual-monitor arm mount to your desk or table. The fast insert function makes it easy to attach your monitor.

The ARMSLIMDUO is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Mount dual displays to the side of your desk or table, with a wide range of adjustment capability
- Ideal for busy work environments such as health care centers, financial and commercial environments
- Spread displays apart or position them back-to-back for multi-user workstations
- Rotate displays to portrait orientation for web design and coding

## Features

- 32 INCH LARGE MONITOR SUPPORT: VESA 75x75/100x100mm compatible full motion multi monitor mount supports 2 displays up to 32" (17.6lb/8kg) per arm; 2 USB 2.0 passthrough ports, 2x 3.5mm audio/mic jacks
- EASY INSTALLATION: This silver monitor mount has a detachable VESA plate w/ quick release clip that makes mounting displays easy & tools incl. for arm balance & tightening c-clamp to desk (up to 60mm)
- CONVENIENT CONNECTIVITY: This desktop monitor mount arm incl. 2 USB-A 2.0 (480Mbps) & 2 3.5mm ports that extend your PC/laptop/computer/dock ports for connecting devices & built-in cable management
- TILT SWIVEL ROTATING: Desk mount dual monitor arm increases ergonomic comfort & productivity w/ -90/+85 tilt, +/-90 swivel & articulating arms support 360 degree screen rotation (landscape/portrait)
- ONE-TOUCH ADJUSTMENT: Max height of 17.7" from the desk, the spring-assisted monitor arm offers toolless adjustable height range of 13.9" and can extend outwards up to 17.7" away from base

---

### Hardware

Warranty	2 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk Clamp

VESA Hole Pattern(s)	75x75 mm
	100x100 mm
Mounting Surface Thickness	Desk Clamp: Max Table Thickness 3.35 in (85 mm)

---

#### Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	15"
Maximum Display Size	32"
Height Adjustment	Yes
Maximum Arm Extension	22.3 in [567.5 mm]
Maximum Arm Span	44.7 in [1135 mm]
Display Tilt	-90 / +85
Display Swivel	180
Swivel / Pivot	135 around the support post 360 at the elbow
Display Rotation	360

---

#### Physical Characteristics

Color	Black
Material	Aluminum
Product Length	0.6 in [1.4 cm]
Product Width	44.7 in [113.5 cm]
Product Height	17.7 in [45.0 cm]
Weight of Product	13.5 lb [6.1 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	9.6 in [24.5 cm]

Package Width 31.8 in [80.8 cm]

Package Height 5.8 in [14.7 cm]

Shipping (Package) Weight 16.2 lb [7.4 kg]

---

#### What's in the Box

Included in Package	1 - mounting arm
	2 - desk clamps (upper bracket)
	2 - desk clamps (lower bracket)
	2 - VESA monitor mounts
	8 - M4x12 mm screws
	8 - M4x30 mm screws
	8 - plastic spacers
	1 - M4 Allen key
	1 - M5 Allen key
	8 - M6x12mm screws
	4 - M8x12 mm screws
	2 - rubber pads
	1 - instruction manual

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***