

Desk Mount Dual Monitor Arm - Ergonomic Dual Monitor VESA Mount 32" (17.6lb/8kg) Displays - Crossbar Handle for Synchronized Full Motion - Height Adjustable - C-Clamp/Grommet

**Product ID:** ARMSLMBARDUO



This Dual Monitor Arm lets you mount two 17" to 32" VESA mount monitors, each weighing up to 17.6 lb. (8 kg), onto a single low-profile base. It gives you flexible desk-clamp or grommet-hole mounting, letting you save space while creating an ergonomic workspace in any office environment.

With a stable crossbar design, the adjustable height dual monitor stand lets you create more usable work space by mounting your monitors side by side on a single base.

The computer screen stand features one-touch height adjustment. The smooth +/- 10 tilt motion and +/- 10 swivel of the individual monitors make it easy to find the optimal viewing angle. You can also rotate each display 360 for portrait or landscape viewing and laterally adjusted along the crossbar length.

The adjustable dual monitor mount is easy to install, with the desk-clamp or grommet mount (hardware included). Integrated cable management keeps your workspace organized. It works well with most desks, including sit-stand workstations.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ARMSLMBARDUO is backed by a 5-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Ideal in office applications including shared workstations with multiple users
- Rotate your display from landscape to portrait position for web design or coding

## Features

- DUAL 32 INCH MONITOR ARM: VESA 75x75/100x100mm compatible heavy-duty desk mount dual monitor arm supports large monitors up to 32" (17.6lb/8kg) per display w/ synchronized full motion articulation
- ONE-TOUCH ADJUSTMENT: Max height of 23.4" from desk, the spring-assisted computer monitor arm w/sturdy handle offers synchronized toolless adjustable height range of 13" & can extend outward up to 23"
- WIDE RANGE OF MOTION: Ergonomic monitor arm increases comfort w/ individual monitor +/-10 tilt, +/-10 swivel, 360 rotating; sliding horizontal crossbar for screen alignment can also swivel 180
- EASY INSTALLATION: C-clamp or grommet mount secures to desk (10mm to 48mm); detachable VESA plate w/ quick release clip makes mounting displays easy; tools incl. to adjust articulating tension
- SMALL FOOTPRINT: Universal desktop multi-monitor mount w/space-saving design enhances the work area & built-in adjustable cable management channels along the arms w/ covers keep cables organized

---

### Hardware

Warranty	5 Years
Wallmountable	No
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.35 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 1.89 in. (10 - 48 mm)

---

### Performance

Weight Capacity (Per Display)	17.6 lb [8 kg]
Minimum Display Size	17"

Maximum Display Size	32"
Height Adjustment	Yes
Display Tilt	+10 / -10
Display Swivel	+10 / -10
Swivel / Pivot	+/- 90 at the crossbar +/- 180 at the shoulder +/- 180 at the elbow
Display Rotation	360

---

#### Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	32.8 in [83.2 cm]
Product Width	22.4 in [56.9 cm]
Product Height	23.4 in [59.5 cm]
Weight of Product	16.1 lb [7.3 kg]

---

#### Packaging Information

Package Quantity	1
Package Length	9.1 in [23.2 cm]
Package Width	35.4 in [90.0 cm]
Package Height	6.3 in [16.1 cm]
Shipping (Package) Weight	19.2 lb [8.7 kg]

---

#### What's in the Box

Included in Package	1 - Base Clamp Assembly 1 - Lower Arm 1 - Upper Arm
---------------------	---

- 1 - Cross Bar
- 2 - VESA Mount
- 1 - Grab Handle
- 1 - Grommet Plate
- 1 - Base Plate
- 1 - Adhesive Foam Pad
- 1 - Cable Management Clip, Base
- 4 - Button Head Hex Screws
- 2 - Flat Head Hex Screws
- 1 - 3mm Hex Key
- 1 - 4mm Hex Key
- 1 - 6mm Hex Key
- 8 - M4 x 12 Screws
- 8 - M5 x 12 Screws
- 8 - Washers
- 4 - Countersunk Screws
- 1 - Grommet Screw
- 1 - Upper C Clamp Bracket
- 1 - Lower C Clamp Assembly

---

**Warranty  
Information**

Warranty	5 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*