1U Vented Server Rack Shelf, 16in (40cm) Mounting Depth, Cantilever Tray For 19" Rack/Cabinet, SPCC Steel, Max 30lb/14kg, Includes Cage Nuts/Screws

Product ID: CABSHELFV1U-16-RACK



This 1U vented rack shelf provides 15.75" (40cm) of usable depth for mounting equipment in any EIA-310-compliant 19-inch rack or cabinet. The vented design helps to improve airflow and maintain optimal temperatures for the mounted equipment. The cantilever tray includes cage nuts and screws for quick deployment.

The fixed-rack shelf is made of 17-gauge (1.4mm) SPCC steel for long-term durability and sturdiness while supporting up to 30lb (14kg) of equipment. Accommodate server rack equipment, accessories, or non-mountable devices for ease of access and connectivity.

The large venting holes on the shelf surface enable improved airflow to dissipate heat and help maintain optimal equipment temperatures.

Certifications, Reports and Compatibility

Applications

Features

• UNIVERSAL 19" FIT: 1U vented rack-mount shelf is designed to fit EIA-310-compliant 19-inch server racks or cabinets; Mounting depth of 15.75 inches (40cm) for data, IT, networking, or non-rack mountable equipment

• MAXIMIZE VENTILATION: The venting holes help promote passive airflow for optimal heat dissipation, maintaining consistent temperatures for the mounted equipment

• STURDY & RELIABLE: Made from 17-gauge SPCC cold-rolled steel, this front-mounted shelf supports up to 30lb

(14kg) and was rigorously stress-tested at 2x the rated capacity, ensuring strength & durability you can count on

• VERSATILE FUNCTIONALITY: Organize non-rackmount devices like routers, modems, UPS systems, or other peripherals and tools in a 19" rack in both professional and personal environments; Ideal for home theaters, sound recording studios, AV setups, and more

• EASY TO INSTALL: Designed to fit in 2 and 4-post server racks; All hardware provided for quick and easy installation

General		
	UPC	065030917124
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Construction Material	Steel
	Product Length	18.9 in [48.1 cm]
	Product Width	15.7 in [39.9 cm]
	Product Height	2.0 in [50 mm]
	Weight of Product	6.1 lb [2.8 kg]
Performance		
	Weight Capacity of Work Surface	30.0 lb [13.6 kg]
	Air Flow Rate	Vented
Hardware		
	Wallmountable	No
	Frame Type	Steel
	U Height	1U
	Cable Management	No
	Tools Included	No
	Industry Standards	EIA/ECA-310-E
	Mounting Surface Thickness	1.4mm (0.05in)

Packaging & In-the-Box		
	Included in Package	1 - 1U 2-Post Vented Shelf
		4 - M5 Screws
		4 - M5 Cage Nuts
		1 - Quick-Start Guide
	Flat Pack (Assembly Required)	Yes
	Package Width	18.7 in [47.5 cm]
	Package Depth	22.0 in [56 cm]
	Package Height	2.6 in [67 mm]
	Shipping (Package) Weight	7.5 lb [3.4 kg]

Product appearance and specifications are subject to change without notice.