

20 Pack Cable Raceway Coupler for CBMWD3816 - Cable Management Accessories - Channel Raceway Fitting Coupler - Midway Connectors - Wiring Duct Straight Connector - UL Rated - TAA

Product ID: CBMWD3816C



This 20-pack of raceway couplers work with the StarTech.com CBMWD3816 raceway system.

Use these cable raceway couplers with the StarTech.com CBMWD3816 raceway to join two of them together and extend the length of your raceway in your office or server room.

Made from sturdy self-extinguishing ABS that's also warp proof, these wiring duct connectors are UL approved with 94HB Flamability (Horizontal Burning) Rating.

Combine this coupler with other StarTech.com CBMWD3816 raceway system accessories to give your cable management solution a finished look.

The End Piece (CBMWD3816E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWD3816I) (20-Pack), joins two raceways together inside of corners at 90 degree angle.

The Lateral Elbow (CBMWD3816L) (20-Pack), joins two raceways together and runs them up the wall at a 90 degree angle.

The Outside Elbow (CBMWD3816O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

The T Connector (CBMWD3816T) (20-Pack), joins three raceways together in T-bar.

This cable management raceway coupler is TAA compliant and backed by a StarTech.com 2-year warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- **GIVE YOUR CABLE MANAGEMENT RACEWAY A FINISHED LOOK:** Use these cable raceway couplers (20 pack) to join two StarTech.com CBMWD3816 raceways & extend length of raceway in office or server room
- **INDUSTRIAL STRENGTH:** Made from sturdy warp-proof ABS, these raceway fitting midway straight connectors are UL approved with 94 HB Flammability (Horizontal Burning) Rating, self-extinguishing
- **OTHER RACEWAY ACCESSORIES:** End Piece (CBMWD3816E), Inside Elbow (CBMWD3816I), Lateral Elbow (CBMWD3816L), Outside Elbow (CBMWD3816O), T Connector (CBMWD3816T); sold separately
- **TECHNICAL SPECIFICATIONS:** Product Length: 1.3" (34.3mm) Connector Width: 1.49" (38mm) Connector Height: 0.63" (16mm) Gray RoHS
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; These wiring duct connectors are backed for 2 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Physical Characteristics

Warranty	2 Years
Color	Gray
Material	ABS
Product Length	1.6 in [4.1 cm]
Product Width	1.2 in [3.0 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	0.1 oz [3.5 g]

Packaging Information

Package Quantity	1
Package Length	5.1 in [12.9 cm]

Package Width	7.3 in [18.5 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	3.0 oz [86.0 g]

What's in the Box

Included in Package	20 - Outside Elbow Connectors
---------------------	-------------------------------

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***