

20 Pack Cable Raceway Outside Corner Connectors for CBMWD3816 - Cable Management Accessories - Channel Raceway Fitting - Wiring Duct 90 Degree Outside Elbow - UL Rated - TAA

**Product ID:** CBMWD3816O



This 20-pack of raceway outside elbows works with the StarTech.com CBMWD3816 raceway system.

Use these cable raceway outside elbows with the StarTech.com CBMWD3816 raceway to join two of them together and run them around corners at a 90 degree angle in your office or server room.

Made from sturdy self-extinguishing ABS that's also warp proof, these wiring duct connectors are UL approved with 94HB Flammability (Horizontal Burning) Rating.

Combine this coupler with other StarTech.com CBMWD3816 raceway system accessories to give your cable management solution a finished look.

The Coupler (CBMWD3816C) (20-Pack), joins two raceways together and extends the length of your raceway.

The End Piece (CBMWD3816E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWD3816I), joins two raceways together inside of corners at 90 degree angle.

The Lateral Elbow (CBMWD3816L), joins two raceways together and runs them up the wall at a 90 degree angle.

The T Connector (CBMWD3816T), joins three raceways together in T-bar.

These cable management raceway outside elbows are TAA compliant and backed by a StarTech.com 2-year warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

## **Certifications, Reports and Compatibility**



## Applications

- Protects cables from damage while neatly routing them in your office or server room

## Features

- GIVE YOUR CABLE MANAGEMENT RACEWAY A FINISHED LOOK: Use cable raceway outside corner connectors (20 pack) w/StarTech.com CBMWD3816 raceways to join them together around corners in your workspace
- INDUSTRIAL STRENGTH: Made from sturdy warp-proof ABS, these Outside elbow cable/wiring duct connectors are UL approved and UL 94HB Flammability (Horizontal Burning) Rating, self-extinguishing
- OTHER RACEWAY ACCESSORIES: Coupler (CBMWD3816C), End Piece (CBMWD3816E), Inside Elbow (CBMWD3816I), Lateral Elbow (CBMWD3816L), T Connector (CBMWD3816T); sold separately
- TECHNICAL SPECIFICATIONS: 90 Angle Connector Width: 1.49" (38mm) Connector Height: 0.63" (16mm) Gray UL approved UL 94HB rated RoHS
- STARTECH.COM ADVANTAGE: IT professionals choice for over 30 years; These raceway outside elbows are backed for 2 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

---

### Physical Characteristics

Warranty	2 Years
Color	Gray
Material	ABS
Product Length	1.3 in [3.3 cm]
Product Width	1.6 in [4.1 cm]
Product Height	1.3 in [3.3 cm]
Weight of Product	0.2 oz [7.0 g]

---

### Packaging Information

Package Quantity	1
Package Length	6.9 in [17.4 cm]

Package Width 6.9 in [17.4 cm]

Package Height 2.6 in [6.7 cm]

Shipping (Package) Weight 5.4 oz [154.0 g]

---

**What's in the Box**

Included in Package 20 - Outside Elbow Connectors

---

**Warranty  
Information**

Warranty 2 Years

---

*\*Product appearance and specifications are subject to change without notice.*

