

20 Pack Cable Raceway L Connector for CBMWWD1911 - 90 Degree Right Angle - Flat L Type - Cable Management Accessories - Channel Raceway/Wiring Duct Fitting Lateral Elbow UL - TAA

Product ID: CBMWWD1911L



This 20-pack of raceway lateral elbows work with the StarTech.com CBMWWD1911 raceway system.

Use these cable raceway lateral elbows with the StarTech.com CBMWWD1911 raceway to join two of them together at a 90 degree angle to extend the length of your raceway up walls in your office or server room.

Made from sturdy self-extinguishing ABS that's also warp proof, these wiring duct elbow connectors are UL approved with 94HB Flamability (Horizontal Burning) Rating.

Combine this lateral elbow with other StarTech.com CBMWWD1911 raceway system accessories to give your cable management solution a finished look.

The Coupler (CBMWWD1911C) (20-Pack), joins two raceways together and extends the length of your raceway.

The End Piece (CBMWWD1911E) (20-Pack), cleanly caps off the end of your raceway.

The Inside Elbow (CBMWWD1911I) (20-Pack), joins two raceways together inside of corners at a 90 degree angle.

The Outside Elbow (CBMWWD1911O) (20-Pack), joins two raceways together around corners at a 90 degree angle.

The T Connector (CBMWWD1911T) (20-Pack), joins three raceways together in T-bar.

These cable management raceway lateral elbows are TAA compliant and backed by a StarTech.com Lifetime warranty and free 24/5 technical support. StarTech.com has been the IT professionals choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Protects cables from damage while neatly routing them in your office or server room

Features

- **GIVE YOUR CABLE MANAGEMENT RACEWAY A FINISHED LOOK:** Use cable raceway L connectors (20 pack) with StarTech.com CBMWWD1911 raceways to join them together at 90 degree angles in your workspace
- **INDUSTRIAL STRENGTH:** Made from sturdy warp-proof ABS, raceway/wiring duct fitting right angle L type flat connectors are UL approved, UL 94HB Flammability (Horizontal Burn) Rated, self-extinguishing
- **OTHER RACEWAY ACCESSORIES:** Coupler (CBMWWD1911C), End Piece (CBMWWD1911E), Inside Elbow (CBMWWD1911I), Outer Elbow (CBMWWD1911O), T Connector (CBMWWD1911T); sold separately
- **TECHNICAL SPECIFICATIONS:** 90 Angle Connector Width: 0.75" (19mm) Connector Height: 0.43" (11mm) White UL approved UL 94HB rated RoHS
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; These lateral elbow connectors are backed for life by StarTech.com, with free 24/5 North America based multi-lingual tech support

Physical Characteristics

Warranty	2 Years
Color	White
Material	ABS
Product Length	1.8 in [4.6 cm]
Product Width	1.8 in [4.6 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.1 oz [3.5 g]

Packaging Information

Package Quantity	1
Package Length	5.0 in [12.8 cm]

Package Width	7.2 in [18.2 cm]
Package Height	1.9 in [4.9 cm]
Shipping (Package) Weight	3.0 oz [86.0 g]

What's in the Box

Included in Package	20 - Lateral Elbow Connectors
---------------------	-------------------------------

**Warranty
Information**

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***