

USB C Multiport Video Adapter with HDMI, VGA, Mini DisplayPort or DVI - USB Type C Monitor Adapter to HDMI 1.4 or mDP 1.2 (4K) - VGA or DVI (1080p) - Silver Aluminum

Product ID: CDPVGDVHDMDP



This silver USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort display. The adapter is also available in Space Gray (CDPVHDMDPSG) and Rose Gold (CDPVHDMDPRG).

Avoid the hassle of carrying different adapters for different displays with this 4-in-1 USB-C adapter. With VGA, DVI, HDMI and mDP output, you can connect your laptop to virtually any display, a convenient plug-and-play solution for travel or Bring Your Own Device (BYOD) applications.

The HDMI and mDP outputs on this USB-C video adapter support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) can support high-definition resolutions of up to 1920 x 1200.

The USB Type-C adapter has an aluminum housing designed to match your silver MacBook and is compatible with any device that supports USB-C DP Alt Mode. Featuring a built-in USB-C cable with magnetic cable manager, the USB-C video adapter conveniently stores away for easy travel.

The CDPVGDVHDMDP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect to virtually any display while traveling
- Connect your BYOD MacBook to a VGA, DVI, HDMI or mDP display at work or school
- Connect a secondary VGA, DVI, HDMI or mDP monitor to your MacBook

Features

- **4-IN-1 MULTIPORT USB-C VIDEO ADAPTER:** USB-C DP Alt Mode to any one of HDMI 1.4 (4K 30Hz & 7.1ch audio), mDP 1.2 (4K 60Hz & 2ch audio), VGA or DVI (1080p), HDCP 2.2/1.4, Thunderbolt 3 compatible
- **TOUGH & PORTABLE:** Durable aluminum Silver enclosure with a magnetically-secured hideaway cable wrap for on-the-go users in the office, at home, boardrooms, and classrooms
- **COMPATIBILITY:** USB-C display adapter for Dell XPS/Precision/Latitude, Lenovo ThinkPad X1 Carbon/Extreme, Surface 3, HP EliteBook/Spectre/ZBook, Chromebooks, TB3 MacBook Pro/Air [Note: The VGA output does not work with M1 based MacBook hosts]
- **TESTED & VERIFIED:** USB Type-C adapter tested @ 4K mini DisplayPort (60Hz)/HDMI (30Hz) or 1080p VGA/DVI with TV, monitor & projector brands like Dell, Asus, Acer, LG, Samsung, Sharp, Sony, Epson
- **EASY TO USE:** Supporting a driverless plug-and-play setup, this adapter is fully compatible with multiple OS platforms: Windows / macOS / Linux / Chrome OS

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	USB-C
AV Output	HDMI - 1.4
	DVI-I (Digital Only) - Single-Link
	VGA
	Mini DisplayPort - 1.2
Chipset ID	Cypress - CYPD1120
	Cypress - CY7C65210
	Parade - PS8348B
	Parade - PS171

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Video Revision	DisplayPort 1.2
	HDMI 1.4
Maximum Analog Resolutions	1920 x 1200 @ 60Hz
Maximum Digital Resolutions	3840 x 2160 @ 30Hz
Supported Resolutions	Max HDMI output: 3840 x 2160 @ 30Hz
	Max mDP output: 3840 x 2160 @ 60Hz
	HDMI and mDP output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720
	DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio
	DVI - No Audio Support
	VGA - No Audio Support
	Mini DisplayPort - 5.1 Channel Audio
General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
MTBF	654,111 hours

Connector(s)

Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode
Connector B	1 - Mini-DisplayPort (20 pin)
	1 - VGA (15 pin, High Density D-Sub)
	1 - DVI-D (25 pin)

1 - HDMI (19 pin)

Special Notes / Requirements

System and Cable Requirements	Your USB-C port must support DisplayPort over USB-C (DP Alt mode) in order to work with this adapter.
Note	Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling The VGA output does not work with M1, M1 PRO, and M1 MAX MacBook hosts

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	40%-50%RH

Physical Characteristics

Color	Silver
Cable Length	4.3 in [110 mm]
Product Length	4.1 in [10.5 cm]
Product Width	2.2 in [5.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	3.8 oz [108 g]

Packaging Information

Package Quantity	1
Package Length	6.9 in [17.6 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	6.1 oz [174.0 g]

What's in the Box

Included in Package	1 - travel A/V adapter
---------------------	------------------------

**Warranty
Information**

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

