

Computer Tower Cart, Rolling Mobile CPU Caddy on Wheels/Casters, Max Load 46.3lb/21kg, Adjustable PC Case Mount, Desktop Floor Stand, Steel Dolly, TAA

**Product ID:** CPUMOBILESTND



This Rolling Computer Tower Stand provides a secure and mobile stand for a desktop computer. The computer caddy allows for full access to the front and back of a CPU tower and ensures a clear path for optimal airflow. The durable steel construction, combined with protective anti-slip pads, safeguards your CPU chassis from damage, making it a reliable solution for workstation applications.

Adjusting the width of the bracket is easy with the toolless adjustment. Use the wing nuts on the bottom of the base to expand the holder from 4.9 to 8.2 inches (125 to 208mm). This flexibility allows the rolling holder to accommodate various case sizes, including UPS battery backups, providing a custom fit for the installed device.

Maximize your desk space by offloading your desktop computer to the mobile cart. The casters at the base enable effortless positioning wherever needed, and the brakes ensure it stays securely in place. With a maximum weight capacity of 46.3 pounds (21kg), this cart is designed to support equipment while keeping the workspace organized.

Experience hassle-free access to your PC's drive bays, peripheral ports, and cables with the under-desk adjustable mobile caddy. The quick assembly process, requiring only three main components, and the inclusion of all necessary hardware make setup simple and straightforward. This practical design keeps your tech easily accessible.

## Certifications, Reports and Compatibility



## Applications

- Easily access to ports, cables, or the back of the computer for maintenance or upgrades

- Position under a desk to free up space

## Features

- **ROLLING CPU CART:** This mobile open frame computer stand provides full access to the front and back of the CPU tower while also providing a clear path for airflow; Protective anti-slip pads prevent damage to the CPU chassis; Durable steel construction
- **TOOLLESS ADJUSTMENT:** Easily adjust the width of CPU mounting bracket using the wing nuts on the bottom of the base; Toolless adjustment from 4.9 - 8.2in (125 - 208mm) enables the CPU cart to accommodate different case sizes or even UPS battery backups
- **SPACE-SAVING:** Use this mobile cart to maximize workspace by offloading the computer tower to the floor or under a desk; The included casters on the CPU holder enable easy positioning, and brakes ensure it stays in place; Max. weight capacity 46.3lb (21kg)
- **HASSLE-FREE:** Access the PC's drive bays, peripheral ports, and cables when mounted on the mobile caddy; Quick assembly with only three main components; All necessary hardware included
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer bracket on wheels is backed for 5-Years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	5 Years
Wallmountable	No
Casters	Included

---

### Performance

General Specifications	Weight Capacity: 46.3lb [21kg]
Adjustable Width: from 4.9in to 8.2in [125mm to 208mm]	

---

### Physical Characteristics

Color	Black
Material	Steel
Product Length	10.1 in [25.7 cm]
Product Width	10.2 in [26.0 cm]
Product Height	10.6 in [27.0 cm]
Weight of Product	7.4 lb [3.4 kg]

**Packaging  
Information**

Package Quantity	1
Package Length	3.1 in [8.0 cm]
Package Width	11.4 in [29.0 cm]
Package Height	11.6 in [29.5 cm]
Shipping (Package) Weight	8.2 lb [3.7 kg]

---

**What's in the Box**

Included in Package	4 - Casters
	2 - Side Walls
	1 - Base
	2 - Side Walls Anti-Slip Pads
	1 - Base Anti-Slip Pad
	4 - Assembly Screws
	4 - Wing Nuts
	4 - Washers
	1 - Wrench
	1 - Quick-Start Guide

---

**Warranty  
Information**

Warranty	5 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

